



Ethernet cable, M12 to RJ45

P/N: T128390ACC

Copyright

© 2015, FLIR Systems, Inc.

All rights reserved worldwide. Names and marks appearing herein are either registered trademarks or trademarks of FLIR Systems and/or its subsidiaries. All other trademarks, trade names or company names referenced herein are used for identification only and are the property of their respective owners.

Document identity

Publ. No.: T128390ACC

Release:

Commit: 29700

Language: en-US

Modified: 2015-10-16

Formatted: 2015-10-20

Disclaimer

Specifications subject to change without further notice. Camera models and accessories subject to regional market considerations. License procedures may apply. Products described herein may be subject to US Export Regulations. Please refer to exportquestions@flir.com with any questions.





| | |
|---------------------------------------|---|
| General description | |
| Ethernet cable, M12 to RJ45, X-coded. | |
| Physical data | |
| Weight | 0.089 kg (0.20 lb.) |
| Cable length | 2 m (6.6 ft.) |
| Connector | M12 to RJ45 |
| Color | Black |
| Shipping information | |
| List of contents | • Cable |
| Packaging, weight | 0.14 kg (0.31 lb.) |
| Packaging, size | 202 × 146 × 25 mm (8.0 × 5.7 × 1.0 in.) |
| EAN-13 | 4743254001794 |
| UPC-12 | 845188009946 |
| Country of origin | Estonia |

Compatible with the following products

- 71201-0101; FLIR AX8 9 Hz



| REV. | DESCRIPTION | DATE |
|------|----------------------------|-------------|
| A | ISSUE | Dec/23/2013 |
| B | Modify the wire diagram. | Dec/25/2013 |
| C | Modify M12 Pin Assignment. | Dec/25/2013 |
| D | Modify cable length. | Dec/25/2013 |
| D1 | Correct key direction. | Jan/22/2014 |
| E | Add note. | Mar/30/2014 |
| F | Modify P/N. | Sep/25/2014 |



| | | | | |
|-----------|--|-----|----------------|-------|
| PLUG | RJ45 8P8C PLUG. | 1 | 78018P8C30A | |
| E | CAT5E FTP 24AWG x 4 PAIR + AL/MY + Drain wire, OD:6.0mm. | 1 | WAC2B0026 | BLACK |
| NUT | Brass, Nickel Plated. | 1 | M12F-RN | |
| W | Viton. | 1 | M12-O-VK | BLACK |
| FACT | Brass , Female pin ,6 u" Gold plated . | 8 | AASPF-1008-0.8 | |
| VECTOR | M12 X-coding Female connector insert. Nylon+GF. | 1 | M12X-08F | BLACK |
| ITEM NAME | DESCRIPTION | QTY | REMARKS | COLOR |

| UNIT: mm | SCALE | TITLE |
|----------|-------|---------------------------------------|
| 1:1 | 1:1 | M12 X-Coding Female Molded Cable Assy |

| UNLESS OTHERWISE SPECIFIED TOLERANCES: | P/N: | DR. |
|--|------------|-----|
| X ± 0.25 | K129351004 | |
| XX ± 0.1 | | CH. |
| XXX ± 0.05 | | AP. |

| REV. | SHEET | DWG.NO. |
|------|-------|---------|
| F | 1/1 | T128390 |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Teledyne FLIR:](#)

[T128390ACC](#)