




Datasheet

LL01CR-CZXxxL06

Available Distribution



Dimensions



Part Number	Diameter	Height
LL01CR-CZXxxL06	Ø71.8	44.8

*All dimensions are in millimeters.

LED



Packaging Details (SPQ)



Recommand Applications



General Information



- Lens Material PMMA 8N
- Operating Temperature -40°C~+70°C
- UL Flammability HB @1.5mm
- UL RTI Elec 90°C @1.5mm
- Light Transmission Rate 400nm~900nm > 90%
- ✓ If necessary, Clean lenses with mild soap, water and soft cloth.
- ⚠ Never use any commercial cleaning solvents on lenses, like alcohol.
- ⚠ Please handle or install with wearing gloves, skin oils may damage lens or its optical characteristic.

Accessories




- Available with Connector
LL01CRZO15Hx (CREE CXA1520)
LL01CRWC15H2 (CREE CXA18xx)

Mechanical Specification

*All dimensions are in millimeters.


Lens Dimension



Connector Dimension



LL01CRZO15Hx




Assembly Instruction

Fixing Method

Part No LL01CR-CZXxxL06
Connector LL01CRZO15Hx
LED CREE CXA1520




Luminaire Accessories



Connector Dimension



LL01CRWC15H2



Assembly Instruction

Fixing Method







Part No LL01CR-CZXxxL06
Connector LL01CRWC15H2
LED CREE CXA18xx



Luminaire Accessories



Photometric Distribution

Lens		
	CREE CXA1520	CREE CXA18xx
15°		
24°		
38°		

Details by LED

Part No	Connector	LED Size	LED
LL01CR-CZX××L06	 LL01CRZO15H×	LES Ø8.9	 CREE CXA1520
	 LL01CRWC15H2	LES Ø12	 CREE CXA18xx

LED	Part No	FWHM	cd / lm	IES
	LL01CR-CZX15L06	12°	9.0	
	LL01CR-CZX24L06	22°	3.8	
	LL01CR-CZX38L06	33°	2.0	

LED	Part No	FWHM	cd / lm	IES
	LL01CR-CZX15L06	14°	6.2	
	LL01CR-CZX24L06	23°	3.5	
	LL01CR-CZX38L06	36°	1.7	

Product Nomenclature

Ledlink Led Type Lens Angle
LL 01 CR -CZX 15 L06
Lens Dot Number Serial Number Type of Material

Ledlink Optics, Inc

Taiwan HQ

15F, No.655, Bannan Rd., Chung-Ho Dist.,
New Taipei City, Taiwan 235

Ledlink Optics (Dongguan) Co., Ltd

Dongguan Factory

No.6, Gaoxin Road, Tiankeng, Hengli Town, Dongguan City,
Guangdong Province, China 523478

Ledlink Optics (Yangzhou) Co., Ltd

Yangzhou Factory

No.180, LinJiang Rd., YangZhou City, Jiangsu Province, China 225009

www.ledlink-optics.com

service@ledlink-optics.com



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[LedLink Optics:](#)

[LL01CRWC15H2](#) [LL01CR-CZX38L06](#)