

EYE ON THE HOG

The Rock-Solid
Judge of the 2010
Vancouver Olympics



No more guessing!


Electronic handles
automatically detect
hog-line violations!

Avoid controversial hog-line calls:

Impartial judging is critical to fun and fair play. The Eye on the Hog electronic handles make hog-line-violation detection easy, leaving no room for human error or controversial judge calls that can cost you the game.

Here is how it works:

Eye on the Hog automatically activates when the rock is tilted for cleaning, immediately sensing when a bare hand touches the handle. Operation is completely intuitive. Upon a valid release, you'll see a green light. If it's in violation, you'll see a red flash. It's that simple. No more guesswork or controversial calls. To conserve battery life, Eye on the Hog circuitry turns off automatically when not in use, allowing you to play like a pro for more than 150 games.



As seen in the 2010 Vancouver Olympic Games!



Special Club Package Offer:

- 16 electronic handles (8 of each color)
- 4 spare electronic handles (2 of each color)
- 20 battery packs
- 2 hog-line magnets
- Magnet Positioning Jig
- Optional shipping case

Get this Special Club Package Offer
today! Call Littelfuse Startco at
306-373-5505 or visit www.eyeonthehog.ca

 **Littelfuse®**
STARTCO

306-373-5505 | www.eyeonthehog.ca



TECHNICAL SPECIFICATIONS:

Handle

Activation:	70° tilt with bare hand touching handle grip
Hog-Line Sensor Accuracy:	3 mm at 3.0 m/s (0.12" at 10 ft/s)
Indication:	
Activation:	Red LED's on momentarily
Verify On/Ready:	Rapid flashing green without hand contact (10 s)
Standby:	Green flash every 2 s following Ready. Returns to Ready when grip is touched and released. Turns off if grip is not touched within 120 s
Delivery:	No indication with hand touching grip
Release:	Rapid flashing green until rock crosses hog-line magnet
Valid:	Solid green
Violation:	Flashing red
Low Battery:	Alternating red and green for 3 s after activation
Mounting torque:	9.5 N•m (84 in-lb) maximum

Battery Pack

Type:	Poly-Carbon Mono Fluoride Lithium (CF Li)
Typical Life:	150 games. Verification tests reduce battery life
Long-Term Storage:	90% residual capacity after 10 years
Battery Disposal:	Dispose in the normal municipal-waste stream

Hog-Line Magnets

Dimensions:	
Height:	5 mm (0.2")
Width:	25 mm (1")
Length:	1524 mm (60")
Placement:	
Centre-Line Position:	One rock radius in front of the leading edge of the hog line
Maximum Depth:	25 mm (1")



Ordering Information

Handles:

R101-H-R	Red curling rock handle
R101-H-Y	Yellow curling rock handle
R101-H-BK	Black curling rock handle
R101-H-BL	Blue curling rock handle

Required Accessories:

R101-B	Battery Pack <i>(order separately)</i>
R101-M	Hog-Line Magnet <i>(2 per sheet, Positioning guide included)</i>
R101-MLJ	Hog-Line Magnet Locating Jig
R101-HSC	Shipping Case for 20 handles <i>(Optional)</i>



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Littelfuse:](#)

[R101-B](#) [R101-H-R](#) [R101-HSC](#) [R101-H-Y](#) [R101-M](#) [R101-MLJ](#) [R101-SHG](#) [R101-TQW](#)