



Carling Technologies®
/// NOW PART OF




Littelfuse®

LTA-Series

Single Pole Lighted Rocker & Paddle Switches

PRODUCT WEBPAGE

request sample, configure part



The illuminated predecessor to the Corvette series whose versatility has allowed it to stand the test of time. Traditional styling coupled with self cleaning contacts, integrated wire leads, and various actuator choices has made the LTA-Series appeal to a wide range of markets.

1
Pole

10-15
Amps

125-250
VAC

6-24
VDC

Typical Applications

- Appliances
- Transportation
- Medical
- HVAC
- Commercial Food

Tech Specs

Dielectric Strength

UL/CSA: 1000V - live to dead metal parts
750V - across open contacts

Electrical Life

100,000 cycles

Operating Temperature

32°F to 185°F (0°C to 85°C)

Ordering Scheme

Sample
Part Number

LTA201 - P R - B - A / 125N

Selection

1

2

3

4

5

6

1. SERIES

10A 250VAC; 15A 125VAC; 3/4 HP 125-250VAC

OFF-NONE-ON Solder Lugs LTA200 .250 Tabs LTA201 .187 Tabs LTA203 Wire Leads LTA205

2. ACTUATOR STYLE

3

T Rocker PS Short Paddle
P Paddle

3. ACTUATOR COLOR

1

A Amber B Black 4
C Clear W White 4
R Red
G Green 2

4. BEZEL COLOR

1

B Black W White

5. LENS COLOR

2,3

Blank No Lens -G Green
-A Amber -R Red
-C Clear -LU Blue

6. LAMP VOLTAGE

2

006V 6V incandescent 024V 24V incandescent
012V 12V incandescent 125N 125V neon
018V 18V incandescent 250N 250V neon

Notes:


- 1 Additional ratings and colors are available. Consult factory for details.
- 2 Neon lamps not recommended with green or blue rocker/lenses.
- 3 Lens color is specified only if actuator style is P or PS. If style is T (rocker), then leave position 5 blank.
- 4 Available with paddle ("P & PS") style actuators only.

[Configure Complete Part Number >](#)




[Browse Standard Parts >](#)

Dimensional Specs

inches [millimeters]



 .069 [1.75] DIA .250 [6.35]	 .156 [3.96] DIA .375 [9.52] .250 [6.35]	 .055 [1.40] DIA .250 [6.35] .187 [4.74]	 6.000 [152.40] .500 [12.70]
TERMINAL TYPE			



Authorized Sales Representatives and Distributors

Click on a region of the map below to find your local representatives and distributors or visit www.carlingtech.com/findarep.



About Carling

Founded in 1920, Carling Technologies is a leading manufacturer of electrical and electronic switches and assemblies, circuit breakers, electronic controls, power distribution units, and multiplexed power distribution systems. With six ISO9001 and IATF16949 registered manufacturing facilities and technical sales offices worldwide, Carling Technologies Sales, Service and Engineering teams do much more than manufacture electrical components, they engineer powerful solutions! To learn more about Carling please visit www.carlingtech.com/company-profile.

To view all of Carling's environmental, quality, health & safety certifications please visit www.carlingtech.com/environmental-certifications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Carling Technologies:](#)

[LTA201-TR-B/125N](#) [LTA201-TR-B/12V](#) [LTA105-TR-BXHC2](#) [LTA211-TG-W/24V](#) [LTA211-PB-B-LU/125N](#) [LTA201-TG-B//125](#) [LTA201-TR-B/012](#) [LTA201-TR-B/018V](#) [LTA221-PB-B-R/125N](#) [LTA201-TC-B/G012](#) [LTA205-TG-B/024V](#)
[LTA201-TR-W/6V](#) [LTA225-PB-B-R/125N](#)