



BF-Inline Fuse Rated 32V

Inline fuse to protect specific cable cross-sections and insulations; Cross-section 10mm² to 35mm². For rated voltage up to 32 VDC.

Assembly notes: The wire integrated fuse has to be insulated by using a self-adhesive shrinking tube. The wire has to be fixed on both sides of the fuse to minimize the wire forces. Recommended shrinking tube: DERAY(R)-IAKT 4:1, 24mm

Specifications

Voltage Rating:	32 VDC
Housing Material:	PETGF30
Insulating Housing Material:	PAGF30
Terminals:	Crimp, Copper alloy, tinned
Interrupting Rating:	2000A @32VDC

Ordering Information

Part Number	Package Size
153.0000	300

Time-Current Characteristics 100A-190A

% of Rating	Opening Time Min / Max (s)	
100	360,000 s	—
150	90 s	1800 s
200	3 s	240 s
300	0.3 s	60 s
500	0.1 s	10 s


Time-Current Characteristics 300A

% of Rating	Opening Time Min / Max (s)	
75	360,000 s	—
165	10 s	100 s
200	1 s	15 s
350	0.3 s	5 s
500	0.1 s	1 s

Ratings

Part Number	Current Rating (A)	Wire Size/Type/ Marking	Typ. Voltage Drop (mV)	Cold Resistance (mΩ)	I ² t (A ² s)
153.1002	100	10mm ² /FLY/P	60	0.42	27,000
153.1012	125	10mm ² /FL2G/S	70	0.32	87,500
153.1602	125	16mm ² /FLY/P	75	0.41	29,600
153.1612	170	16mm ² /FL2G/S	60	0.22	248,000
153.2502	170	25mm ² /FLY/P	70	0.29	78,500
153.2512	190	25mm ² /FL2G/S	52	0.22	248,000
153.3502	300	35mm ² /FLY/P	70	0.20	373,000

Time-Current Characteristics Curve



Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

[153.3502](#) [153.1602](#) [153.2512](#) [153.1002](#) [153.2502](#) [153.1012](#) [153.1612](#)