









## PGE FAMILY, PGH FAMILY, PGA FAMILY

SENSING RESISTORS		
Product	Features	Accessory For
<b>PGE-600V</b> Sensing Resistor 	Used on systems up to 1 kV.	<b>PGR-5330</b> <b>PGM-8325</b>
<b>PGE-05KV</b> Sensing Resistor 	Used on systems up to 5 kV.	<b>PGR-5330</b> <b>PGM-8325</b>
<b>PGE-15KV</b> Sensing Resistor 	Used on systems up to 15 kV.	<b>PGR-5330</b> <b>PGM-8325</b>
<b>PGE-25KV</b> Sensing Resistor 	Used on systems up to 25 kV.	<b>PGR-5330</b> <b>PGM-8325</b>
<b>PGE-35KV</b> Sensing Resistor 	Used on systems up to 35 kV.	<b>PGR-5330</b>

TERMINATIONS AND ADAPTERS		
Product	Features	Accessory For
<b>PGH-5000</b> High Tension Couplers 	Allows 5-kV systems to be connected to relay.	<b>PGR-3200</b> <b>PGR-6100</b> <b>PGR-8600</b>
<b>PGH-6000</b> High Tension Couplers 	Allows 6-kV systems to be connected to relay.	<b>PGR-3200</b> <b>PGR-6100</b> <b>PGR-8600</b>
<b>PGA-0TA6</b> Termination Assembly 	50 W ground-check termination with convenient mounting holes and screw terminals, temperature compensated.	<b>PGM-8134</b>
<b>PGA-0TA7</b> Small-Format Termination Assembly with Wire Leads 	12 W ground-check termination, ideal for use in end caps and submersible pumps. Mounting holes and wire leads, temperature compensated.	<b>PGM-8134</b>
<b>PGA-0400</b> Port-Powered Serial Converter 	Converts an RS-485 signal to an RS-232 signal, used for set-point programming and updating flash memory.	<b>PGR-6200</b> <b>PGR-6300</b> <b>PGR-7200</b>
<b>PGA-0420</b> Serial Connector Adapter Kit 	Connects an RJ45 socket to a 9-pin serial connector, includes 1.5 m cable and plug-in adapter.	<b>PGR-6200</b> <b>PGR-7200</b>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Littelfuse:](#)

[PGA-0420](#) [PGA-0400](#) [PGA-0TA7](#) [PGA-0TA6](#)