


LED Displays ~ Seven Segment ~ Numeric



Single Digit




Features/Options

- ▶ Standard and high brightness chips
- ▶ Intensity grading available
- ▶ Custom sizes at minimal tooling
- ▶ Face and segment off colors in grey and milky white

Applications/Uses

- ▶ Test instruments
- ▶ Diagnostic equipment
- ▶ Instrument and control panels
- ▶ Monitoring displays


2.3" single digit



Part Number	Wave Length (nm)	Brightness (μcd) @ 10mA	Vf (typ) 10mA*	Vf (max) 10mA*	Emitted Color	Polarity (common)
LDS-AD12RI	565	2500	8.8 / 4.4	10.4 / 5.2	Green	Anode
LDS-AD14RI	635	2500	8.0 / 4.0	10.0 / 5.0	Red	Anode
LDS-AD16RI	660	8000	6.8 / 3.4	8.8 / 4.4	Red	Anode
LDS-AD12RI-SUG	574	7000	8.8 / 4.4	10.4 / 5.2	Green	Anode
LDS-AD14RI-SI	636	15,000	8.0 / 4.0	10.4 / 5.2	Red	Anode
LDS-AD17RI-USB	470	6000	14.0 / 7.0	16.0 / 8.0	Blue	Anode
LDS-CD12RI	565	2500	8.8 / 4.4	10.4 / 5.2	Green	Cathode
LDS-CD14RI	635	2500	8.0 / 4.0	10.0 / 5.0	Red	Cathode
LDS-CD16RI	660	8000	6.8 / 3.4	8.8 / 4.4	Red	Cathode
LDS-CD12RI-SUG	574	7000	8.8 / 4.4	10.4 / 5.2	Green	Cathode
LDS-CD14RI-SI	636	15,000	8.0 / 4.0	10.4 / 5.2	Red	Cathode
LDS-CD17RI-USB	470	6000	14.0 / 7.0	16.0 / 8.0	Blue	Cathode

Second value for dual chips in decimal point

4.0" single digit



Part Number	Wave Length (nm)	Brightness (μcd) @ 10mA	Vf (typ) 10mA*	Vf (max) 10mA*	Emitted Color	Polarity (common)
LDS-AA402RI	565	2500	8.8 / 4.4	10.4 / 5.2	Green	Anode
LDS-AA404RI	635	2500	8.0 / 4.0	10.0 / 5.0	Red	Anode
LDS-AA406RI	660	8000	6.8 / 3.4	8.8 / 4.4	Red	Anode
LDS-AA402RI-SUG	574	7000	8.8 / 4.4	10.4 / 5.2	Green	Anode
LDS-AA404RI-SI	636	15,000	8.0 / 4.0	10.4 / 5.2	Red	Anode
LDS-AA407RI-USB	470	6000	14.0 / 7.0	16.0 / 8.0	Blue	Anode
LDS-CA402RI	565	2500	8.8 / 4.4	10.4 / 5.2	Green	Cathode
LDS-CA404RI	635	2500	8.0 / 4.0	10.0 / 5.0	Red	Cathode
LDS-CA406RI	660	8000	6.8 / 3.4	8.8 / 4.4	Red	Cathode
LDS-CA402RI-SUG	574	7000	8.8 / 4.4	10.4 / 5.2	Green	Cathode
LDS-CA404RI-SI	636	15,000	8.0 / 4.0	10.4 / 5.2	Red	Cathode
LDS-CA407RI-USB	470	6000	14.0 / 7.0	16.0 / 8.0	Blue	Cathode

Second value for dual chips in decimal point



USA/Canada +1-800-278-5666
Europe +49-6081-964380
Asia +886-3-5821124



www.lumex.com



USA/Canada +1-847-359-8904
Europe +49-6081-964381
Asia +886-3-5821154

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Lumex:](#)

[LDS-AA406RI](#) [LDS-CA406RI](#) [LDS-AA402RI](#) [LDS-CA404RI](#) [LDS-AA404RI](#)