



PANEL HOLE: Ø0.250"
PANEL THICKNESS: 0.030" MIN.

*UNLESS OTHERWISE SPECIFIED TOLERANCES PER DECIMAL PRECISION ARE: X=±1 (±0.039), XX=±0.5 (±0.020), XXX=±0.25 (±0.010), XXXX=±0.127 (±0.005), LEAD SIZE=±0.05 (±0.002), LEAD LENGTH=±0.75 (±0.030), MIN=-0.00

REV.

PART NUMBER

SSI-LXH600GHW-400

T-5mm (T-1 3/4) LED, PANEL MOUNT INDICATOR,
GREEN/RED BICOLOR LED, MILKY WHITE DIFFUSED LENS,
WITH 16" WIRE LEADS.

PART NUMBER

SSI-LXH600GHW-400

REV.

ELECTRO-OPTICAL CHARACTERISTICS TA=25°C If=20mA

PARAMETER	MIN	TYP	MAX	UNITS	TEST COND
PEAK WAVELENGTH		565 (GREEN) 700 (RED)		nm	
FORWARD VOLTAGE (G/R)		2.2/2.0	2.6/2.5	Vf	If=100µA
REVERSE VOLTAGE	5.0			Vr	
AXIAL INTENSITY (G/R)		25/6		mcd	If=20mA
VIEWING ANGLE		60		2x theta	
EMITTED COLOR:		GREEN/RED			
EPOXY LENS FINISH:		MILKY WHITE DIFFUSED			

LIMITS OF SAFE OPERATION AT 25°C

PARAMETER	COLORS	MAX	UNITS
PEAK FORWARD CURRENT*		150	mA
STEADY CURRENT		25	mA
POWER DISSIPATION	(G/R)	105/120	mW
DERATE FROM 25°C		-1.2	mW/°C
OPERATING, STORAGE TEMP.		-40 TO +85	°C
SOLDERING TEMP.		+260	°C
2.0mm FROM BODY			3 SEC. MAX

* t<10µs

NOTES:

1. SSL-LX509F3GHW LED.
2. SSH-LXH600 HOLDER, BLACK.
3. RED ANODE LEAD: LXP-WST24RDTC, 24 AWG STRANDED, TOP OVERCOAT, GREEN INSULATION, CUT 415mm LONG, STRIP 4mm & 9.5mm.
4. RED ANODE LEAD: LXP-WST24BLTC, 24 AWG STRANDED, TOP OVERCOAT, BLACK INSULATION, CUT 415mm LONG, STRIP 4mm & 9.5mm.

UNCONTROLLED DOCUMENT

CONFIDENTIAL INFORMATION

THE INFORMATION CONTAINED IN THIS DOCUMENT IS THE PROPERTY OF LUMEX INC. EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY LUMEX INC., THE HOLDER OF THIS DOCUMENT SHALL KEEP ALL INFORMATION CONTAINED HEREIN CONFIDENTIAL AND SHALL PROTECT SAME IN WHOLE OR IN PART FROM DISCLOSURE AND DISSEMINATION TO ALL THIRD PARTIES.

RELIABILITY NOTE

OUR MANY YEARS OF EXPERIENCE DATA ACCUMULATION INDICATE THAT SOLDER HEAT IS A MAJOR CAUSE OF EARLY AND FUTURE FAILURE. PLEASE PAY ATTENTION TO YOUR SOLDERING PROCESS.



290 E. HELEN ROAD
PALATINE, IL 60067-6976
PHONE: +1.847.359.2790
US WEB: www.lumex.com
TW WEB: www.lumex.com.tw

DRAWN BY: BC

CHECKED BY:

APPROVED BY:

DATE: 1.8.03
PAGE: 1 OF 1
SCALE: N/A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumex:

[SSI-LXH600GHW-400](#)