



SMT LEDs ~ Right Angle ~ Molded Carrier



SML-LXR44XC-TR

Right Angle SMT Molded Carrier




Features/Options

- ▶ Molded Package with 2.6 mm Chip Center Off-Board
- ▶ State-of-the-Art LED Die (All Colors)
- ▶ High Volume Capacity Production
- ▶ Focused Light Emission and Reflection
- ▶ Increased Power/Solder
- ▶ Heat Dissipation Over PCB Carrier Types

Applications/Uses

- ▶ Keyboard/Keypad Illumination
- ▶ Display or Character Backlighting
- ▶ Status or Fault Indicators
- ▶ Motion Control Circuits
- ▶ Medical Diagnostic Instruments



SML-LXR44 Package Style - Super Bright

Right Angle SMT Molded Carrier

Lumex Part Number	Die Material	Emitted Color	Peak (nm)	Lens	Axial Intensity @ If=20mA	V _f Typ @ If=20mA	V _f Max @ If=20mA	View Angle° 2θ	Reel Size (pcs)	Reflow Profile Pg. 134	Tape Specs Pg. 134
SML-LXR44SIC-TR	AlInGaP	Super High Intensity Red	636	Clear	170	2.0	2.6	90	500	Figure 3	Figure B
SML-LXR44SOC-TR	AlInGaP	Super Orange	610	Clear	170	2.0	2.5	90	500	Figure 3	Figure B
SML-LXR44SRC-TR	GaAlAs	Super Red	660	Clear	80	1.7	2.2	90	500	Figure 3	Figure B
SML-LXR44SUGC-TR	AlInGaP	Super Ultra Green	574	Clear	210	2.2	2.6	90	500	Figure 3	Figure B
SML-LXR44SYC-TR	AlInGaP	Super Yellow	590	Clear	200	2.0	2.5	90	500	Figure 3	Figure B

SML-LXR44 Package Style - Ultra Bright and White

Right Angle SMT Molded Carrier

Lumex Part Number	Die Material	Emitted Color	Peak (nm)	Lens	Axial Intensity @ If=20mA	Chromaticity Coordinates		V _f Typ @ If=20mA	V _f Max @ If=20mA	View Angle° 2θ	Reel Size (pcs)	Reflow Profile Pg. 134	Tape Specs Pg. 134
						X	Y						
SML-LXR44USBC-TR	InGaN	Ultra Super Blue	470	Clear	170	-	-	3.5	4.0	120	500	Figure 3	Figure B
SML-LXR44UPGC-TR	InGaN	Ultra Pure Green	525	Clear	150	-	-	3.5	4.0	120	500	Figure 3	Figure B
SML-LXR44UWC-TR	InGaN	Ultra White	-	Clear	120	0.33	0.34	3.5	4.0	90	500	Figure 3	Figure B



USA/Canada 1-800-278-5666
Asia +886-3-5821124



www.lumex.com



USA/Canada 1-847-359-8904
Asia +886-3-5821154

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumex:

[SML-LXR44SOC-TR](#) [SML-LXR44USBC-TR](#) [SML-LXR44UWC-TR](#)