



SMT LEDs ~ PCB Carrier ~ Package Style 0603



SML-LXFT0603XC-TR

Flat Solder terminals Ultra Thin PCB




Features/Options

- ▶ Small 0603 Package
- ▶ State-of-the-Art LED Die
- ▶ Wide Angle of Emission
- ▶ High Volume Capacity Production
- ▶ Quick Delivery
- ▶ All Color Choices Available
- ▶ Gold End Contacts
- ▶ Extra Thin Board

Applications/Uses

- ▶ Display or Character Backlighting
- ▶ Status Indicators
- ▶ Circuit Fault Indicators
- ▶ Keyboard Post Lighting
- ▶ Medical Diagnostic Instruments



SML-LXFT0603 Package Style - Super Bright

Flat Solder terminals Ultra Thin PCB

Lumex Part Number	Die Material	Emitted Color	Peak (nm)	Lens	Axial Intensity @ If=20mA	V _f Typ @ If=20mA	V _f Max @ If=20mA	View Angle° 2θ	Reel Size (pcs)	Reflow Profile Pg. 138	Tape Specs Pg. 138
SML-LXFT0603SIC-TR	AlInGaP	Super High Intensity Red	636	Clear	150	2.0	2.6	120	4000	Figure 1	Figure A
SML-LXFT0603SOC-TR	AlInGaP	Super Orange	610	Clear	200	2.0	2.5	120	4000	Figure 1	Figure A
SML-LXFT0603SRC-TR	GaAlAs	Super Red	660	Clear	100	1.7	2.2	120	4000	Figure 1	Figure A
SML-LXFT0603SUGCTR	AlInGaP	Super Ultra Green	574	Clear	50	2.2	2.6	120	4000	Figure 1	Figure A
SML-LXFT0603SYCTR	AlInGaP	Super Yellow	590	Clear	80	2.0	2.5	120	4000	Figure 1	Figure A

SML-LXFT0603 Package Style - Ultra Bright

Flat Solder terminals Ultra Thin PCB

Lumex Part Number	Die Material	Emitted Color	Peak (nm)	Lens	Axial Intensity @ If=20mA	V _f Typ @ If=20mA	V _f Max @ If=20mA	View Angle° 2θ	Reel Size (pcs)	Reflow Profile Pg. 138	Tape Specs Pg. 138
SML-LXFT0603USBC-TR	InGaP	Ultra Super Blue	470	Clear	30	3.5	4.0	120	4000	Figure 1	Figure A
SML-LXFT0603UPGC-TR	InGaP	Ultra Pure Green	525	Clear	45	3.5	4.0	120	4000	Figure 1	Figure A



USA/Canada +1-800-278-5666
Europe +49-6081-964380
Asia +886-3-5821124



www.lumex.com



USA/Canada +1-847-359-8904
Europe +49-6081-964381
Asia +886-3-5821154

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumex:

[SML-LXFT0603SRC-TR](#)