


LED Indicators ~ Panel ~ Dome Lens



SSI-LXR5020XD-150 Series

T-5mm Black Panel Indicator, Flush LED



PANEL CUTOUT: 8.05mm
PANEL THICKNESS: 0.6 - 2.8mm
TERMINATION: 6" 24 AWG Leads

FEATURES / OPTIONS

- ▶ State-of-the-Art, High Brightness LED Chip Technology
- ▶ Choice of LED Colors and Lens Finishes
- ▶ Bi-Color Styles Optional
- ▶ Insulated Lead Lengths Optional
- ▶ Easy Two-Step Installation, Rear and Front of Panel
- ▶ Small Volumes Acceptable
- ▶ Available Without Insulated Leads (Bare LED Pins)
- ▶ Blinking LED
- ▶ With Internal Resistor for 5V and 12V Operation
- ▶ With Connector


APPLICATIONS / USES

- ▶ Front Panel Status Indicators
- ▶ Alarm/Warning Indicators
- ▶ Front Panel Circuit Fault Indicators
- ▶ Instrument Control Panels
- ▶ Medical Diagnostics Indicators
- ▶ Industrial Automation Control Panels

Lumex Part Number	Die Material	Emitted Color	Peak (nm)	Lens	Operating Current (mA)	Operating TYP. Vf (V)	Brightness TYP. Mcd	@ mA	View Angle° 2θ	Component LED Used
HIGH BRIGHTNESS										
SSI-LXR5020SID-150	AlInGaP	Super High Intensity Red	636	Red Diffused	5-25	2	700	20	60	SSL-LX5093SID
SSI-LXR5020SOD-150	AlInGaP	Super Orange	610	Orange Diffused	5-25	2	850	20	60	SSL-LX5093SOD
SSI-LXR5020SUGD150	AlInGaP	Super Ultra Green	574	Green Diffused	5-25	2.2	170	20	60	SSL-LX5093SUGD
SSI-LXR5020SYD-150	AlInGaP	Super Yellow	590	Yellow Diffused	5-25	2	300	20	60	SSL-LX5093SYD
SSI-LXR5020USBD150	InGaN/SiC	Ultra Super Blue	470	Blue Diffused	5-25	3.5	300	20	60	SSL-LX5093USBD
SSI-LXR5020UWW-150	InGaN/SiC	Ultra White	-	White Diffused	5-25	3.5	650	20	30	SSL-LX5093UWW
STANDARD BRIGHTNESS										
SSI-LXR5020GD-150	GaP	Green	565	Green Diffused	5-25	2.2	30	20	60	SSL-LX5093GD
SSI-LXR5020ID-150	GaAsP	High Intensity Red	635	Red Diffused	5-25	2.0	30	20	60	SSL-LX5093ID
SSI-LXR5020SRD-150	GaAlAs	Super Red	660	Red Diffused	5-25	1.8	250	20	60	SSL-LX5093SRD
SSI-LXR5020YD-150	GaAsP	Yellow	585	Yellow Diffused	5-25	2.1	30	20	60	SSL-LX5093YD

SSI-LXR5020XX-3

T-5mm Black Panel Indicator, 3-Leaded Flush LED



PANEL CUTOUT: 8.05mm
PANEL THICKNESS: 0.6 - 2.8mm

FEATURES / OPTIONS

- ▶ State-of-the-Art, High Brightness LED Chip Technology
- ▶ Choice of LED Colors and Lens Finishes
- ▶ Bi-Color Styles Optional
- ▶ Insulated Lead Lengths Optional
- ▶ Easy Two-Step Installation, Rear and Front of Panel
- ▶ Small Volumes Acceptable
- ▶ Wire Leads Termination
- ▶ Blinking LED
- ▶ With Internal Resistor for 5V and 12V Operation
- ▶ With Connector
- ▶ Common Anode Version

APPLICATIONS / USES

- ▶ Front Panel Status Indicators
- ▶ Alarm/Warning Indicators
- ▶ Front Panel Circuit Fault Indicators
- ▶ Instrument Control Panels
- ▶ Medical Diagnostics Indicators
- ▶ Industrial Automation Control Panels

Lumex Part Number	Die Material	Emitted Color	Peak (nm)	Lens	Operating Current (mA)	Operating TYP. Vf (V)	Brightness TYP. Mcd	@ mA	View Angle° 2θ	Component LED Used
SSI-LXR5020IGW-3	GaAsP	High Intensity Red	635	Milky White	5-25	2.0	45	20	60	SSL-LX5099IGW
	GaP	Green	565	Diffused	5-25	2.2	55	20		
SSI-LXR5020IYW-3	GaAsP	High Intensity Red	635	Milky White	5-25	2.0	55	20	60	SSL-LX5099IYW
	GaAsP	Yellow	585	Diffused	5-25	2.1	40	20		
SSI-LXR5020SISUGW3	AlInGaP	Super High Intensity Red	636	Milky White	5-25	2	700	20	60	SSL-LX5099SISUGW
	AlInGaP	Super Ultra Green	574	Diffused	5-25	2.2	200	20		
SSI-LXR5020SISYW-3	AlInGaP	Super High Intensity Red	636	Milky White	5-25	2	800	20	60	SSL-LX5099SISYW
	AlInGaP	Super Yellow	590	Diffused	5-25	2	400	20		
SSI-LXR5020SRSGW-3	GaAlAs	Super Red	660	Milky White	5-25	1.7	200	20	60	SSL-LX5099SRSGW
	GaP	Super Green	565	Diffused	5-25	2.2	60	20		
SSI-LXR5020SYSUGW3	AlInGaP	Super Yellow	590	Milky White	5-25	2	400	20	60	SSL-LX5099SYSUGW
	AlInGaP	Super Ultra Green	574	Diffused	5-25	2.2	200	20		
SSI-LXR5020YGW-3	GaAsP	Yellow	585	Milky White	5-25	2.1	40	20	60	SSL-LX5099YGW
	GaP	Green	565	Diffused	5-25	2.2	45	20		



USA/Canada +1-800-278-5666
Europe +49-6081-964380
Asia +886-3-5821124



www.lumex.com



USA/Canada +1-847-359-8904
Europe +49-6081-964381
Asia +886-3-5821154

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Lumex:

[SSI-LXR5020SID-150](#) [SSI-LXR5020YGW-3](#)