

GEARWRENCH[®] *FORGE AHEAD*



Modular Sets





Modular Tool Sets

Consist of multi-piece assortments of quality GEARWRENCH tools, each organized in a sturdy EVA foam tray. The chemical and solvent resistant trays are designed in multiple modular sizes to fit perfectly with a range tool storage systems. This modular design allows users to customize their own toolkit and storage system. Sets feature components selected to provide a complete range of specific tools, each nested in a custom cutout that protects while keeping tools organized and accessible. Trays are orange and black with high visibility size markings for quick tool identification.

EVA Foam Trays

Premium Solvent Resistant

EVA foam trays built to last and handle almost any working setting, while providing long lasting protection to the set's contents



High Visibility Size Markings

EVA foam trays have GEARWRENCH orange cutouts with black tops that feature high visibility white size markings for quick tool identification

Precut Nested Tool Storage

Each tool nests in a laser-formed cutout that provides protection and keeps tools organized and easily accessible



Each set's tray is perfectly sized to fit a range tool storage units



Drive Tool Modular Tool Sets

86520

Meets or exceeds ASME specifications

Bright, Full Polish Chrome Finish

Easily wipes clean and resists corrosion

Extension Bars

Feature a knurled grip, providing a non slip surface

Flexible Head

Provides access for hard to reach fasteners



Universal Joint

Provide additional access to hard to reach fasteners

90-Tooth Gear

Delivers a 4° swing arc to turn a fastener in tight confines



86521



86522



Item No.	Set Descriptions	Includes
86520	16 Pc. 1/4" Drive Tool Modular Set	1/4" Dr. Full Polish Chrome 90T Ratchet, 1/4" Dr. Full Polish Chrome 90T Flex Head Ratchet, 1/4" Dr. Gimbal Ratchet, 1/4" Dr. Thumbwheel Ratchet, 1/4" Dr. Flex Handle Breaker Bar, 1/4" Dr. Universal Joint, 1/4" Dr. Extension Bars: 2", 3", 4", 6", 10", 1/4" Dr. Wobble Extension Bars: 2", 4", 6", 1/4" Dr. Locking Extension Bars: 2", 3", 6", 1/4" Dr. Adapter: 1/4" F x 3/8" M
86521	21 Pc. 3/8" Drive Tool Modular Set	3/8" Dr. Full Polish Chrome 90T Ratchet, 3/8" Dr. Full Polish Chrome 90T Flex Head Ratchet, 3/8" Dr. Gimbal Ratchet, 3/8" Dr. Thumbwheel Ratchet, 3/8" Dr. Flex Handle Breaker Bars: 12", 18", 3/8" Dr. Universal Joint, 3/8" Dr. Extension Bars: 1-1/2", 3", 6", 10", 12", 3/8" Dr. Wobble Extension Bars: 3", 6", 10", 12", 3/8" Dr. Locking Extension Bars: 3", 6", 10", 3/8" Dr. Adapters: 3/8" F x 1/4" M, 3/8" F x 1/2" M
86522	18 Pc. 1/2" Drive Tool Modular Set	1/2" Dr. Full Polish Chrome 90T Ratchet, 1/2" Dr. Full Polish Chrome 90T Flex Head Ratchet, 1/2" Dr. Flex Handle Breaker Bars, 1/2" Dr. Sliding T Handle, 1/2" Dr. Universal Joint, 1/2" Dr. Extension Bars: 3", 5", 10", 15", 1/2" Dr. Wobble Extension Bars: 5", 10", 15", 1/2" Dr. Locking Extension Bars: 3", 5", 10", 1/2" Dr. Adapter: 1/2" F x 3/8" M

Drive Tool Accessory Modular Set

86523

Meets or exceeds ASME specifications

Bright, Full Polish Chrome Finish

Easily wipes clean and resists corrosion

Extension Bars


Feature a knurled grip, providing a non slip surface

Extensions, Adapter, Universal Joint


Feature a ball detent for secure socket retention

Universal Joint

Provide additional access to hard to reach fasteners



UNIVERSAL JOINT FOR



HARD TO REACH FASTENERS

BALL DETENT



SOCKET RETENTION

LARGE STAMPED SIZES



FOR EASY IDENTIFICATION

OIL & SOLVENT



RESISTANT

Item No.	Set Descriptions	Includes
86523	29 Pc. 1/4", 3/8", 1/2" Drive Tool Accessory Modular Set	1/4" Dr. Extension Bars: 2", 3", 4", 6", 10", 14", 3/8" Dr. Extension Bars: 1-1/2", 3", 6", 10", 1/2" Dr. Extension Bars: 3", 5", 10", 1/4" Dr. Locking Extension Bars: 2", 3", 6", 3/8" Dr. Locking Extension Bars: 3", 6", 10", 1/2" Dr. Locking Extension Bars: 3", 5", 10", Universal Joints: 1/4", 3/8", 1/2", 1/4" Dr. Adapter: 1/4" F x 3/8" M, 3/8" Dr. Adapters: 3/8" F x 1/4" M, 3/8" F x 1/2" M, 1/2" Dr. Adapter: 1/2" F x 3/8" M

Impact Drive Tool Accessory Modular Set

86524

Meets or exceeds ASME specifications

Chrome Molybdenum Alloy Steel (Cr-Mo)

For exceptional strength and durability

High-Visibility Laser Etched Markings

Provide quick size identification

Manganese Phosphate Finish

To resist corrosion

Extensions, Adapter, Universal Joint


Feature a ball detent for secure socket retention

Universal Joint

Provide additional access to hard to reach fasteners



UNIVERSAL JOINT FOR



HARD TO REACH FASTENERS

BALL DETENT



SOCKET RETENTION

HIGH VISIBILITY MARKING



FOR EASY IDENTIFICATION

CHROME MOLYBDENUM



STRENGTH AND DURABILITY

Item No.	Set Descriptions	Includes
86523	17 Pc. 1/4", 3/8", 1/2" Impact Drive Tool Accessory Modular Set	1/4" Dr. Impact Extension Bars: 2", 4", 6", 3/8" Dr. Impact Extension Bars: 3", 6", 10", 15", 1/2" Dr. Impact Extension Bars: 3", 5", 10", 15", Impact Universal Joints: 1/4", 3/8", 1/2", 1/4" Dr. Impact Adapter: 1/4" F x 3/8" M, 3/8" Dr. Impact Adapters: 3/8" F x 1/4" M, 3/8" F x 1/2" M, 1/2" Dr. Impact Adapter: 1/2" F x 3/8" M

Ratchet & Bolt Biter Sockets Modular Set

86525


Meets or exceeds ASME specifications

90-Tooth Gear

Delivers a 4° swing arc to turn a fastener in tight confines

Full Polish Chrome Extension Bar

Providing more access to additional fasteners



Sockets Made From Chrome Molybdenum Alloy Steel (Cr-Mo)
For exceptional strength and durability

Bi-Directional Design
For removing or tightening damaged fasteners

High-Visibility Laser Etched Markings
Provide quick size identification

Item No.	Set Descriptions	Includes
86525	31 Pc. SAE/MM Bolt Biter Ratchet Socket Modular Set	3/8" Dr. Full Polish Chrome 90T Ratchet, 3/8" Dr. Extension Bar: 3", 3/8" Dr. Bolt Biter Extraction Sockets: 3/8"-, 3/8", 10-mm, 10mm, 11-mm(7/16"-), 11mm(7/16"), 12-mm, 12mm, 13-mm(1/2"), 13mm, 14-mm, 14mm(9/16"-), 9/16", 16-mm(5/8"-), 16mm(5/8"), 17-mm, 17mm, 11/16"-, 11/16", 19-mm(3/4"-), 19mm(3/4"), 3/8" Dr. Adapter: 3/8" F x 1/4" M, 1/4" Dr. Bolt Biter Extraction Sockets: 1/4"-, 1/4", 7-mm, 7mm, 8-mm(5/16"-), 8mm(5/16")

72T Combination Ratcheting Wrench Modular Tool Sets

86526

Meets or exceeds ASME specifications

72-Tooth Ratcheting Box End

Needs a minimal 5° to move fasteners vs. 30° for standard wrenches

Stubby Beam Length

For when clearance is limited

Size Conveniently Stamped on Both Ends of the Beams

For quick identification

Thin Head and Beam

Provide greater access in confined work areas



Off-Corner Loading Design

On box end provides better grip and reduces fastener rounding

86527



OFF-CORNER LOADING



5° SWING ARC



LARGE SIZE STAMPING



PASS THROUGH DESIGN



Item No.	Set Descriptions	Includes
86526	21 Pc. SAE Standard & Stubby Length Combination Ratcheting Wrench Modular Set	72T Full Polish Chrome Combination Ratcheting Wrenches: 1/4", 5/16", 11/32", 3/8", 7/16", 1/2", 9/16", 5/8", 11/16", 3/4", 13/16", 7/8", 15/16", 1", 72T Full Polish Chrome Stubby Combination Ratcheting Wrenches: 3/8", 7/16", 1/2", 9/16", 5/8", 11/16", 3/4"
86527	28 Pc.. MM Standard & Stubby Length Combination Ratcheting Wrench Modular Set	72T Full Polish Chrome Combination Ratcheting Wrenches: 6mm, 7mm, 8mm, 9mm, 10mm, 11mm, 12mm, 13mm, 14mm, 15mm, 16mm, 17mm, 18mm, 19mm, 20mm, 21mm, 22mm, 24mm. 72T Full Polish Chrome Stubby Combination Ratcheting Wrenches: 10mm, 11mm, 12mm, 13mm, 14mm, 15mm, 16mm, 17mm, 18mm, 19mm

90T Combination Ratcheting Wrench & Hex Key Modular Set

86528

Meets or exceeds ASME specifications

Thin Head and Beam

Provide greater access in confined work areas

Chamfered Edges

On both ends of the hex key help guide the key into the fastener

Size Conveniently Stamped on Both Ends of the Beams

For quick identification



90-Tooth Ratcheting Box End

Delivers a 4° swing arc to turn a fastener in tight spaces

Off-Corner Loading Design

On box end provides better grip and reduces fastener rounding

OFF-CORNER LOADING



LARGE SIZE STAMPING



4° SWING ARC



CHAMFERED EDGE




Item No.	Set Descriptions	Includes
86528	41 Pc. SAE/MM 90T Combination Ratcheting Wrench & Hex Key Modular Set	90T Full Polish Chrome Combination Ratcheting Wrenches: 1/4", 5/16", 3/8", 7/16", 1/2", 9/16", 5/8", 11/16", 3/4", 13/16", 8mm, 9mm, 10mm, 11mm, 12mm, 13mm, 14mm, 15mm, 16mm, 17mm, 18mm, 19mm, Long Arm Hex Keys: 0.050", 1/16", 5/64", 3/32", 7/64", 1/8", 9/64", 5/32", 3/16", 7/32", 1/4", 5/16", 3/8", 1.5mm, 2mm, 2.5mm, 3mm, 4mm, 5mm, 6mm, 8mm, 10mm

90T Modular Mechanics Tool Set

86529

Meets or exceeds ASME specifications



Item No.	Set Descriptions	Includes
86529	83 Pc 90T 1/4", 3/8", 1/2" Dr. SAE/MM 90T Modular Mechanics Tool Set	90T Full Polish Chrome Ratchets: 1/4" 3/8", 1/2", Flex Handle Breaker Bar: 1/4", Extension Bars: 1/4" Dr. – 3", 6"; 3/8" Dr. – 3", 6"; 1/2" Dr. – 5", 10", 1/4" Dr. 6pt Sockets: 4mm, 5mm, 5.5mm, 6mm, 7mm, 8mm, 9mm, 10mm, 11mm, 12mm, 13mm, 14mm, 15mm, 5/32", 3/16", 7/32", 1/4", 9/32", 5/16", 11/32", 3/8", 7/16", 1/2", 9/16", 1/2" Dr. 12pt. Sockets: 19mm, 20mm, 21mm, 23mm, 24mm, 25mm, 26mm, 27mm, 28mm, 29mm, 30mm, 3/8", 7/16", 1/2", 9/16", 5/8", 3/4", 11/16", 13/16", 7/8", 15/16", 1", 1-1/16", 1-1/8", 1-3/16", 1-1/4", 1-1/2" 3/4", 3/8" Dr. 6pt. Sockets: 10mm, 11mm, 12mm, 13mm, 14mm, 15mm, 16mm, 17mm, 18mm, 19mm, 3/8", 7/16", 1/2", 9/16", 5/8", 11/16", Universal Joints: 1/4", 3/8", 1/2", Adapters: 1/4" Dr. – 1/4" F x 3/8" M, 3/8" Dr. – 3/8" F x 1/4" M, 3/8" F x 1/2" M, 1/2" Dr. – 1/2" F x 3/8" M



Item No.	Descriptions	Width	Depth	Height
86520	16 Pc. 1/4" Drive Tool Modular Set	14.3"	13.5"	2.0"
86521	21 Pc. 3/8" Drive Tool Modular Set	20.7"	13.5"	2.0"
86522	18 Pc. 1/2" Drive Tool Modular Set	20.7"	13.5"	2.0"
86523	29 Pc. 1/4", 3/8", 1/2" Drive Tool Accessory Modular Set	20.7"	13.5"	2.0"
86524	17 Pc. 1/4", 3/8", 1/2" Impact Drive Tool Accessory Modular Set	20.7"	13.5"	2.0"
86525	31 Pc. SAE/MM Bolt Biter Ratchet Socket Modular Set	14.3"	13.5"	2.0"
86526	21 Pc. SAE Standard & Stubby Length Combination Ratcheting Wrench Modular Set	20.7"	13.5"	2.0"
86527	28 Pc. MM Standard & Stubby Length Combination Ratcheting Wrench Modular Set	20.7"	13.5"	2.0"
86528	41 Pc. SAE/MM 90T Combination Ratcheting Wrench & Hex Key Modular Set	20.7"	13.5"	2.0"
86529	83 Pc. 90T 1/4", 3/8", 1/2" Dr. SAE/MM 90T Modular Mechanics Tool Set	20.7"	13.5"	2.0"

[illegible]

Modular Set Dimensions & Compatibility with GSX Tool Storage

Item No.	Descriptions	Drawer	Tray Width	Depth	Height	86520	86521	86522	86523	86524	86525	86526	86527	86528	86529
83245	41" 11 Drawer Cabinet	Top	36.8"	15.0"	4.8"	X	X	X	X	X	X	X	X	X	X
		Top Left	20.7"	15.0"	4.8"	X	X	X	X	X	X	X	X	X	X
		Middle Left 1	20.7"	15.0"	3.0"	X	X	X	X	X	X	X	X	X	X
		Middle Left 2	20.7"	15.0"	3.0"	X	X	X	X	X	X	X	X	X	X
		Middle Left 3	20.7"	15.0"	3.0"	X	X	X	X	X	X	X	X	X	X
		Bottom Left	20.7"	15.0"	6.1"	X	X	X	X	X	X	X	X	X	X
		Top Right	13.7"	15.0"	9.2"	X					X				
		Middle Right 1	13.7"	15.0"	3.0"	X					X				
		Middle Right 2	13.7"	15.0"	3.0"	X					X				
		Middle Right 3	13.7"	15.0"	6.1"	X					X				
		Bottom Right	13.7"	15.0"	9.2"	X					X				
83246	36" 7 Drawer Cart	Top	30.0"	18.0"	2.9"	X	X	X	X	X	X	X	X	X	X
		Middle 1	30.0"	18.0"	2.9"	X	X	X	X	X	X	X	X	X	X
		Middle 2	30.0"	18.0"	2.9"	X	X	X	X	X	X	X	X	X	X
		Middle 3	30.0"	18.0"	2.9"	X	X	X	X	X	X	X	X	X	X
		Middle 4	30.0"	18.0"	2.9"	X	X	X	X	X	X	X	X	X	X
		Middle 5	30.0"	18.0"	2.9"	X	X	X	X	X	X	X	X	X	X
		Bottom	30.0"	18.0"	6.1"	X	X	X	X	X	X	X	X	X	X
83169	42" 11 Drawer Mobile Work Station	Top	36.8"	15"	4.8"	X	X	X	X	X	X	X	X	X	X
		Top Left	20.7"	15"	3"	X	X	X	X	X	X	X	X	X	X
		Middle Left 1	20.7"	15"	3"	X	X	X	X	X	X	X	X	X	X
		Middle Left 2	20.7"	15"	3"	X	X	X	X	X	X	X	X	X	X
		Middle Left 3	20.7"	15"	6.1"	X	X	X	X	X	X	X	X	X	X
		Bottom Left	20.7"	15"	9.2"	X	X	X	X	X	X	X	X	X	X
		Top Right	13.7"	15"	3"	X					X				
		Middle Right 1	13.7"	15"	3"	X					X				
		Middle Right 2	13.7"	15"	3"	X					X				
		Middle Right 3	13.7"	15"	6.1"	X					X				
		Bottom Right	13.7"	15"	9.2"	X					X				
83168	33" 3 Drawer Cart	Till	31.7"	18.5"	4.9"	X	X	X	X	X	X	X	X	X	X
		Top Left	13.2"	17.4"	2.7"										
		Top Right	13.2"	17.4"	2.7"										
		Middle	27.5"	17.4"	2.7"	X	X	X	X	X	X	X	X	X	X
		Bottom	27.5"	17.4"	6.7"	X	X	X	X	X	X	X	X	X	X
		Bottom Tray	32.1"	20.2"	3.2"	X	X	X	X	X	X	X	X	X	X
83167	33" 2 Drawer Cart	Till	31.7"	18.5"	4.9"	X	X	X	X	X	X	X	X	X	X
		Top	27.5"	17.4"	2.7"	X	X	X	X	X	X	X	X	X	X
		Bottom	27.5"	17.4"	2.7"	X	X	X	X	X	X	X	X	X	X
		Bottom Tray	32.1"	20.2"	3.2"	X	X	X	X	X	X	X	X	X	X
83166	Adjustable Mobile Work Table	Table	30"	20"	N/A	X	X	X	X	X	X	X	X	X	X



Modular Tool Sets Compatibility with GSX Storage

The Modular Sets offering is compatible with GEARWRENCH GSX cabinets and chests, allowing users to customize and build their own toolkit and storage system.



Apex Tool Group, LLC
1000 Lufkin Road
Apex, NC 27539
www.apextoolgroup.com
©2021 Apex Tool Group, LLC



ATG-7340
GEARWRENCH® is registered as a trademark of Apex Brands, Inc.,
a Division of Apex Tool Group, LLC
Specifications subject to change without notice.

FORGE AHEAD

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apex Tool Group:](#)

[86522](#) [86529](#) [86526](#) [86524](#) [86527](#) [86521](#) [86520](#) [86525](#) [86523](#) [86528](#)