



1096



Basic Part Number	# of Wraps	Wrapost Length A
1096-2	2	.381
1096-3	3	.527

1096-X-05-XX-00-00-01-0
Press-fit in .057 mounting hole


1106



Basic Part Number	# of Wraps	Wrapost Length A
1106-2	2	.370
1106-3	3	.510


1106-X-23-XX-00-00-01-0
Press-fit in .057 mounting hole

1093




1093-0-05-XX-00-00-01-0
Press-fit in .056 mounting hole

0730




0730-3-05-XX-00-00-01-0
Press-fit in .057 mounting hole

1122




1122-0-22-XX-00-00-01-0
Press-fit in .053 mounting hole

1064




1064-0-23-XX-00-00-01-0
Press-fit in .056 mounting hole

1092




1092-0-05-XX-00-00-01-0
Press-fit in .056 mounting hole

1068



1068-0-23-XX-00-00-01-0
Press-fit in .057 mounting hole

1070 ⇒ 1072



107X-X-23-XX-00-00-01-0
Press-fit in .057 mounting hole

Basic Part Number	# of Wraps	Wrapost Length A
1072-1	1	.260
1071-2	2	.370
1070-3	3	.510

SPECIFICATIONS

PIN MATERIAL:
Brass Alloy 360, 1/2 Hard

DIMENSION IN INCHES
TOLERANCES ON:
LENGTHS: ±.005
DIAMETERS: ±.002
ANGLES: ± 2°

ORDER CODE: XXXX - X - XX - XX - 00 - 00 - 01 - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 200μ" TIN/LEAD OVER NICKEL
- ◇ 80 200μ" TIN OVER NICKEL (RoHS)
- ◇ 15 10μ" GOLD OVER NICKEL (RoHS)
- ◇ 21 20μ" GOLD OVER NICKEL (RoHS)



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[1122-0-22-80-00-00-01-0](#) [1106-3-23-80-00-00-01-0](#) [1096-3-05-80-00-00-01-0](#) [1093-0-05-80-00-00-01-0](#) [1092-0-05-80-00-00-01-0](#) [1071-2-23-80-00-00-01-0](#) [1070-3-23-80-00-00-01-0](#) [1068-0-23-80-00-00-01-0](#) [1093-0-05-01-00-00-01-0](#) [1096-3-05-01-00-00-01-0](#) [1096-2-05-01-00-00-01-0](#) [1092-0-05-01-00-00-01-0](#) [1072-1-23-01-00-00-01-0](#) [1071-2-23-01-00-00-01-0](#) [1070-3-23-01-00-00-01-0](#) [1068-0-23-01-00-00-01-0](#) [1064-0-23-15-00-00-01-0](#) [1064-0-23-21-00-00-01-0](#) [1070-3-23-21-00-00-01-0](#) [1071-2-23-15-00-00-01-0](#) [1071-2-23-21-00-00-01-0](#) [1072-1-23-21-00-00-01-0](#) [1092-0-05-21-00-00-01-0](#) [1093-0-05-15-00-00-01-0](#) [1093-0-05-21-00-00-01-0](#) [1096-2-05-15-00-00-01-0](#) [1096-2-05-21-00-00-01-0](#) [1096-3-05-15-00-00-01-0](#) [1096-3-05-21-00-00-01-0](#) [1122-0-22-15-00-00-01-0](#)