



- Series 551 PGA Interconnect sockets are available in various lengths with .019" dia. pluggable solder tails at one end and .025" dia. pins at the other.*
- Hi-Temp PCT polyester insulator material suitable for all forms of soldering.




Ordering Information

HEADER PIN TYPE 03




1. Select pin type for PGA header at left to determine 2-digit suffix designation, and enter under pin type.
2. Specify 2-digit plating code from chart at bottom of page.
3. Locate footprint pattern from pages 107 to 111, the middle 8 digits of the part number will be located under the pattern.



Determined from footprint pattern pages 107 to 111

HEADER PIN TYPE 04, 05




Pin Type

04	For L = .331"
05	For L = .606"

EXAMPLE OF COMPLETE PART NUMBER:

551-10-068-11-061004

This is a 68 pin (11x11 grid) insulator with a .6" square window and fitted with 551...004 header pins. Pins are gold plated.



*Many other printed circuit pins are available for use in addition to those listed above. See pages 170 to 173. Consult Mill-Max Applications Engineers to develop a part number for your specific requirement.



SPECIFY PLATING CODE XX=	10◇	90	40◇	
Pin Plating 	10μ" Au	200μ" Sn/Pb	200μ" Sn	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[551-10-179-15-041004](#) [551-10-225-15-000004](#) [551-10-225-15-000005](#) [551-10-225-18-091003](#) [551-10-240-17-061004](#) [551-10-109-12-051003](#) [551-10-114-15-063003](#) [551-10-101-13-061005](#) [551-10-121-15-061003](#) [551-10-124-14-071005](#) [551-10-145-13-041004](#) [551-10-155-16-003005](#) [551-10-168-17-105004](#) [551-10-173-16-005004](#) [551-10-176-15-061004](#) [551-10-179-15-041005](#) [551-10-179-18-095003](#) [551-10-223-18-098004](#) [551-10-225-18-091005](#) [551-10-241-18-075004](#) [551-10-289-17-000005](#) [551-10-299-20-096003](#) [551-10-324-18-000004](#) [551-10-324-18-000005](#) [551-90-012-05-001004](#) [551-90-025-05-000005](#) [551-90-028-06-005003](#) [551-90-036-06-000003](#) [551-90-045-08-005004](#) [551-90-056-09-041003](#) [551-90-056-09-041004](#) [551-90-064-08-000005](#) [551-90-072-09-001005](#) [551-90-073-11-042005](#) [551-10-121-11-000003](#) [551-10-121-15-061004](#) [551-10-133-14-071003](#) [551-10-323-21-005004](#) [551-10-361-19-000005](#) [551-10-383-22-105003](#) [551-10-240-17-061005](#) [551-90-025-05-000003](#) [551-90-044-08-031005](#) [551-90-072-09-001003](#) [551-90-072-11-061004](#) [551-90-072-11-061005](#) [551-90-073-11-042003](#) [551-90-076-11-041004](#) [551-90-084-10-031003](#) [551-10-383-22-105005](#) [551-10-441-21-000004](#) [551-10-441-21-000005](#) [551-90-032-01-503005](#) [551-90-052-09-045004](#) [551-90-052-09-045005](#) [551-90-064-08-000004](#) [551-10-159-16-105005](#) [551-10-173-16-005003](#) [551-10-196-14-000005](#) [551-10-223-18-098003](#) [551-10-256-19-081005](#) [551-10-273-21-125003](#) [551-90-032-09-041005](#) [551-90-045-08-005005](#) [551-90-064-10-051004](#) [551-90-068-11-061003](#) [551-90-084-10-031005](#) [551-90-059-11-001004](#) [551-90-065-10-051004](#) [551-90-076-11-041003](#) [551-90-084-11-041003](#) [551-90-032-09-041004](#) [551-90-064-10-051003](#) [551-90-068-10-041005](#) [551-90-072-09-001004](#) [551-90-073-11-042004](#) [551-90-081-09-000003](#) [551-90-081-09-000004](#) [551-10-177-15-061003](#) [551-10-181-15-041005](#) [551-10-209-17-081003](#) [551-10-224-18-095003](#) [551-10-238-19-086003](#) [551-10-273-21-125004](#) [551-10-273-21-125005](#) [551-90-022-05-001003](#) [551-90-028-06-005005](#) [551-90-036-06-000004](#) [551-90-036-06-000005](#) [551-90-049-07-000003](#) [551-90-064-10-051005](#) [551-90-072-11-042003](#) [551-10-114-15-063005](#) [551-10-132-14-071004](#) [551-10-114-13-061003](#) [551-10-114-13-061005](#) [551-10-128-13-041004](#) [551-10-133-13-045004](#) [551-10-136-14-051004](#) [551-10-144-12-000005](#)