

INTERCONNECTS

SERIES 416 • 2,54 GRID ELEVATED • DOUBLE ROW STRIPS




FIG. 1




FIG. 2




FIG. 3




FIG. 4




FIG. 5

- Elevated socket strips are available in 5 different heights:

416...006 uses pin # 0153-1

416...003 uses pin # 0153-2

416...007 uses pin # 0153-3


416...008 uses pin # 0153-4

416...001 uses pin # 0153-5

See page 167 for details

- Hi-Rel, 4-finger BeCu #30 contact is rated at 3 amps. See page 253 for details

- Insulators are high temperature thermoplastic, suitable for all soldering operations



ORDERING INFORMATION

FIG. 1	Series 416...006	Standoff Height = 5,99		
	416-XX-2	-41-006000		
	Specify number of pins	04-64		
FIG. 2	Series 416...003	Standoff Height = 8,0		
	416-XX-2	-41-003000		
	Specify number of pins	04-64		
FIG. 3	Series 416...007	Standoff Height = 10,21		
	416-XX-2	-41-007000		
	Specify number of pins	04-64		
FIG. 4	Series 416...008	Standoff Height = 11,99		
	416-XX-2	-41-008000		
	Specify number of pins	04-64		
FIG. 5	Series 416...001	Standoff Height = 15,09		
	416-XX-2	-41-001000		
	Specify number of pins	04-64		
RoHS-2 2011/65/EU XX=Plating Code See Below For Electrical, Mechanical & Environmental Data, See page 264				
SPECIFY PLATING CODE XX=				
Sleeve (Pin)	91	93	41	43
Contact (Clip)	0,25µm Au	0,76µm Au	0,25µm Au	0,76µm Au

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[416-91-212-41-007000](#) [416-91-212-41-008000](#) [416-91-216-41-003000](#) [416-91-220-41-001000](#) [416-91-226-41-003000](#) [416-91-226-41-006000](#) [416-91-236-41-006000](#) [416-91-240-41-001000](#) [416-91-210-41-006000](#) [416-91-226-41-007000](#) [416-91-230-41-007000](#) [416-91-234-41-001000](#) [416-91-234-41-003000](#) [416-91-240-41-007000](#) [416-91-244-41-003000](#) [416-91-214-41-003000](#) [416-91-220-41-003000](#) [416-91-224-41-001000](#) [416-91-224-41-003000](#) [416-91-212-41-003000](#) [416-91-212-41-006000](#) [416-91-218-41-006000](#) [416-91-224-41-008000](#) [416-91-226-41-001000](#) [416-91-228-41-006000](#) [416-91-228-41-008000](#) [416-91-216-41-001000](#) [416-91-222-41-003000](#) [416-91-222-41-006000](#) [416-91-232-41-003000](#) [416-91-242-41-003000](#) [416-91-216-41-006000](#) [416-91-222-41-008000](#) [416-91-230-41-001000](#) [416-91-230-41-003000](#) [416-91-232-41-007000](#) [416-91-232-41-008000](#) [416-91-236-41-003000](#) [416-91-242-41-008000](#) [416-91-246-41-003000](#) [416-91-250-41-001000](#) [416-91-250-41-003000](#) [416-91-260-41-003000](#) [416-91-262-41-007000](#) [416-91-256-41-006000](#) [416-93-208-41-008000](#) [416-93-212-41-003000](#) [416-93-212-41-007000](#) [416-93-216-41-001000](#) [416-93-222-41-006000](#) [416-93-238-41-007000](#) [416-93-242-41-007000](#) [416-93-246-41-001000](#) [416-93-246-41-003000](#) [416-93-258-41-008000](#) [416-93-260-41-001000](#) [416-91-262-41-006000](#) [416-91-264-41-008000](#) [416-93-204-41-007000](#) [416-93-218-41-003000](#) [416-93-224-41-008000](#) [416-91-212-41-001000](#) [416-93-228-41-006000](#) [416-93-232-41-001000](#) [416-93-232-41-003000](#) [416-93-248-41-006000](#) [416-91-240-41-003000](#) [416-91-246-41-006000](#) [416-91-256-41-003000](#) [416-91-260-41-001000](#) [416-93-206-41-001000](#) [416-93-208-41-007000](#) [416-93-212-41-006000](#) [416-93-226-41-001000](#) [416-93-236-41-003000](#) [416-93-238-41-008000](#) [416-93-248-41-008000](#) [416-93-256-41-001000](#) [416-93-256-41-003000](#) [416-91-226-41-008000](#) [416-91-230-41-006000](#) [416-91-244-41-001000](#) [416-91-254-41-001000](#) [416-91-258-41-001000](#) [416-91-260-41-006000](#) [416-93-204-41-001000](#) [416-93-226-41-006000](#) [416-93-230-41-001000](#) [416-93-230-41-003000](#) [416-93-236-41-007000](#) [416-93-240-41-001000](#) [416-91-232-41-006000](#) [416-91-234-41-008000](#) [416-91-242-41-006000](#) [416-91-244-41-008000](#) [416-91-246-41-001000](#) [416-91-252-41-003000](#) [416-91-256-41-001000](#) [416-91-210-41-008000](#) [416-91-214-41-006000](#)