

0548	8975	3016	9548															
0548-0-15-XX-21-XX-10-0 Solder mount in .036 min. mounting hole	8975-0-15-XX-21-XX-10-0 Solder mount in .036 min. mounting hole	3016-0-15-XX-21-XX-10-0 Solder mount in .036 min. mounting hole	9548-0-15-XX-21-XX-10-0 Solder mount in .036 min. mounting hole															
8637	1407	0553/8553																
8637-0-15-XX-21-XX-10-0 Solder mount in .037 min. mounting hole	1407-0-15-XX-11-XX-10-0 Solder mount in .040 min. mounting hole	<table><tr><th>Basic Part Number</th><th>Length L</th><th>Depth N</th></tr><tr><td>0553-1</td><td>.140</td><td>.124</td></tr><tr><td>0553-2</td><td>.170</td><td>.154</td></tr><tr><td>0553-3</td><td>.282</td><td>.266</td></tr><tr><td>8553-0</td><td>.245</td><td>.229</td></tr></table> X553-X-15-XX-X1-XX-10-0 Hex press-fit in .041 plated thru hole		Basic Part Number	Length L	Depth N	0553-1	.140	.124	0553-2	.170	.154	0553-3	.282	.266	8553-0	.245	.229
Basic Part Number	Length L	Depth N																
0553-1	.140	.124																
0553-2	.170	.154																
0553-3	.282	.266																
8553-0	.245	.229																
0566	0442	0554																
<table><tr><th>Basic Part Number</th><th>Length L</th></tr><tr><td>0566-1</td><td>.083</td></tr><tr><td>0566-2</td><td>.138</td></tr></table> 0566-X-15-XX-21-XX-10-0 Solder mount in .039 min. mounting hole	Basic Part Number	Length L	0566-1	.083	0566-2	.138	0442-0-15-XX-11-XX-10-0 Solder mount in .040 min. mounting hole	0554-0-15-XX-21-XX-10-0 Solder mount in .040 min. mounting hole										
Basic Part Number	Length L																	
0566-1	.083																	
0566-2	.138																	
SPECIFICATIONS SHELL MATERIAL: Brass Alloy 360, 1/2 Hard CONTACT MATERIAL: Beryllium Copper Alloy 172, HT DIMENSION IN INCHES TOLERANCES ON: LENGTHS: ±.005 DIAMETERS: ±.002 ANGLES: ± 2° ORDER CODE: XXXX - X - 15 - XX - XX - XX - 10 - 0 BASIC PART # → SPECIFY SHELL FINISH: → 01 200μ" TIN/LEAD OVER NICKEL 15 10μ" GOLD OVER NICKEL SPECIFY CONTACT FINISH: → 02 200μ" TIN/LEAD OVER NICKEL 14 10μ" GOLD OVER NICKEL 27 30μ" GOLD OVER NICKEL SELECT CONTACT #11 or #21 CONTACT (DATA ON PAGE 206)																		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[0442-0-15-15-11-14-10-0](#) [8975-0-15-15-21-14-10-0](#)