

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0008550102](#)
Status: **Active**
Overview: [KK Interconnect Solutions](#)
Description: KK 254 Crimp Terminal, 22-30 AWG, Bag, Selective Gold (Au), Nickel (Ni) Under Plating

Documents:

Drawing (PDF)	Packaging Specification PK-2759-001-001 (PDF)
Product Specification 50510002-PS-000 (PDF)	Test Summary TS-10-07-001 (PDF)
Product Specification PS-10-07-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	2759
Application	Signal, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	KK Interconnect Solutions
Packaging Alternative	08550101 (Reel)
Product Name	KK 254
UPC	800753745995

Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Nickel
Net Weight	0.064/g
Packaging Type	Bag
Plating min - Mating	0.381µm
Plating min - Termination	0.762µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.57mm max.
Wire Size AWG	22, 24, 26, 28, 30
Wire Size mm ²	N/A

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	2759-(555)L
--------------------	-------------

Reference - Drawing Numbers

Packaging Specification	PK-2759-001-001
Product Specification	50510002-PS-000, PS-10-07-001
Sales Drawing	SD-2759-001
Test Summary	TS-10-07-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[2759](#) Series

Use With

[2695](#) , [5051](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction Tool for KK 2.54mm Terminals, 22-30 AWG	11030022
PremiumGrade Hand Crimp Tool for KK 2.54mm Crimp Terminals, 22-30 AWG	638118200

Insertion Tool for KK 638120000
2.54mm Terminals,
22-30 AWG

This document was generated on 09/02/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[08-55-0102](#)