

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0008520124

Status:

Active

Overview:

KK Interconnect Solutions

Description:

KK Trifurcon Crimp Terminal 7258, 22-26 AWG, Reel, Phosphor Bronze Tin(Sn)

Documents:

Drawing (PDF)

Product Specification PS-40-02-001 (PDF)

Packaging Specification PK-2759-002-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	7258
Application	Power, Wire-to-Board
Crimp Quality Equipment	Yes
Overview	KK Interconnect Solutions
Packaging Alternative	08520125 (Loose)
Product Name	KK, Trifurcon
UPC	800753756700
Physical	
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.159/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.65mm max.
Wire Size AWG	22, 24, 26
Wire Size mm²	N/A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	7258-A(P909)
Reference - Drawing Numbers	
Packaging Specification	PK-2759-002-001
Product Specification	PS-40-02-001
Sales Drawing	SD-7258-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

Green Image

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Low-Halogen

Status

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

7258 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extraction Tool for Flat Blade, 3.96mm KK, 2.00mm, 3.96mm EdgeMate, and Ultra-Fit Terminals	11030016
Terminator Die	11402097
Terminator Die	11402099
PremiumGrade Hand Crimp Tool for KK 3.96mm Terminals, 22-26 AWG	638117400
Mini-Mac Applicator	638881000

This document was generated on 09/22/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[08-52-0124 \(Mouser Reel\)](#) [08-52-0124 \(Cut Strip\)](#)