

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0010021042](#)
Status: **Active**
Overview: [KK 508 Connector System](#)
Description: KK PC Board Connector, Bottom Entry Mount Style B, 1.00µm Tin (Sn), 4 Circuits

Documents:
[3D Model](#) [Packaging Specification PK-3002-002-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-99020-0087-001 \(PDF\)](#)

Agency Certification

CSA LR19980
UL E29179

General

Product Family PCB Receptacles
Series [3002](#)
Application Board-to-Board, Power
Overview [KK 508 Connector System](#)
Product Name KK 508
UPC 800753745322

Physical


Circuits (Loaded) 4
Circuits (maximum) 4
Color - Resin Natural
Durability (mating cycles max) 25
Flammability 94V-2
Glow-Wire Capable No
Material - Metal Phosphor Bronze
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Nylon
Net Weight 1.020/g
Number of Rows 1
Orientation Bottom Entry
PC Tail Length 4.10mm
PCB Locator No
PCB Retention None
PCB Thickness - Recommended 1.60mm
Packaging Type Tray
Pitch - Mating Interface 5.08mm
Pitch - Termination Interface 5.08mm
Plating min - Mating 1.016µm
Plating min - Termination 1.016µm
Polarized to PCB No
Temperature Range - Operating See Product Specification
Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 7.0A
Voltage - Maximum 250V

Solder Process Data

Duration at Max. Process Temperature (seconds) 005
Lead-freeProcess Capability WAVE
Max. Cycles at Max. Process Temperature 001
Process Temperature max. C 260



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/71/2019 (16 July
2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[3002](#) Series

Mates With

Headers [3003](#) , [2599](#) , [3061](#)

Material Info

Engineering Number 300204B

Reference - Drawing Numbers

Packaging Specification PK-3002-002-001
Product Specification PS-99020-0087-001
Sales Drawing SDAE-3002-NB
Symbol/Footprint Data SYM-1002-1042

This document was generated on 09/15/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[10-02-1042](#)