

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION


Part Number: 0011402096
Status: Active
Overview: Application Tooling
Description: Terminator Die

Documents:
RoHS Certificate of Compliance (PDF)

General
Product Family Application Tooling
Series 207122
Function Crimp
Geographic Area Global
Level of Automation Semi-Automatic
More Detailed Tech Information applicationtooling@molex.com
Overview Application Tooling
Product Name N/A
Tool Type Terminator Die
UPC 800753621114
Warranty Disclaimer CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Material Info
Engineering Number T8301AX

Reference - Drawing Numbers
Application Tooling Documents
ATS-011402096-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001, TM-638500090-001, TM-638500090SP-001



Series image - Reference only

EU ELV
Not Reviewed

EU RoHS
Not Reviewed
REACH SVHC
Not Reviewed
Halogen-Free
Status
Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Not Reviewed

Not Reviewed

Not Reviewed

Search Parts in this Series
207122 Series

Use With
Molex TM-42 Press 690025001 and Base Unit 11193001 for the 3BF Press

Application Tooling Description	FAQ Product #
KK 396 Crimp Terminal 2478, 18-24 AWG, Reel, Brass Tin (Sn)	8500105
KK 396 Crimp Terminal 2478, 18-24 AWG, Reel, Phosphor Bronze, Tin (Sn)	8520071
KK Trifurcon Crimp Terminal 6838, 18-20 AWG, Reel, Phosphor Bronze Tin(Sn)	8520112
KK 396 Crimp Terminal 2478, 18-24 AWG, Reel, Brass,	8560105

	0.51µm Selective Gold (Au)	
	KK 396 Crimp	<u>8580121</u>
	Terminal 2478, 18-24 AWG, Reel, Phosphor Bronze, 0.51µm Selective Gold (Au)	
	KK Trifurcon Crimp	<u>8580187</u>
	Terminal 6438, 18-20 AWG, Reel, Phosphor Bronze Gold (Au)	
	KK 396 Crimp	<u>8650114</u>
	Terminal 2478, 18-24 AWG, Reel, Phosphor Bronze, 0.38µm Selective Gold (Au)	
	3.96mm Pitch	<u>1721601803</u>
	EdgeMate Crimp Terminal, Phosphor Bronze, Tin (Sn), Bifurcated, 18-20 AWG, Reel	
	3.96mm Pitch	<u>1721601805</u>
	EdgeMate Crimp Terminal, Brass, Gold (Au), Bifurcated, 18-20 AWG, Reel	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[11-40-2096](#)