

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0015291027](#)
Status: **Active**
Overview: [C-Grid Connector Products](#)
Description: 2.54mm Pitch C-Grid Shunt Terminal Housings, 0.762µm Gold (Au), 2 Circuits, with Pin Stop

Documents:

3D Model	Packaging Specification PK-70873-0815-001 (PDF)
Drawing (PDF)	Test Summary TS-7859-0001-001 (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-7859-001 (PDF)	

Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Accessories
Series	7859
Component Type	Shunt
Overview	C-Grid Connector Products
Product Name	C-Grid, C-Grid III, SL
UPC	800753604414

Physical

Circuits (Loaded)	2
Circuits (maximum)	2
Color - Resin	Black
Flammability	94V-0
Lock to Mating Part	No
Material - Metal	Phosphor Bronze
Material - Resin	Polyester
Net Weight	0.164/g
Number of Rows	1
Packaging Type	Bag
Temperature Range - Operating	-40° to +105°C

Electrical

Current - Maximum per Contact	5.0A
-------------------------------	------

Solder Process Data


Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	7859-2A561N
--------------------	-------------

Reference - Drawing Numbers

Packaging Specification	PK-70873-0815-001
Product Specification	PS-7859-001
Sales Drawing	SDA-7859-2AXXXN-001
Test Summary	TS-7859-0001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[7859](#) Series

Use With

[70280](#) C-Grid Breakaway Header, [71308](#) C-Grid Header, [71764](#) C-Grid Breakaway Header, [42375](#) KK Breakaway Header, [42377](#) KK Breakaway Header, [4030](#) KK Wire-to-Board Header, [42152](#) KK Wire-to-Board Header

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

15-29-1027