

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [0019092017](#)  
**Status:** **Active**  
**Overview:** [Standard .093" Pin and Socket Connectors](#)  
**Description:** 2.36mm Diameter Standard .093" Pin and Socket Plug Housing with Positive Latch, UL 94V-0, with Panel Mount, 1 Circuit

**Documents:**  
[3D Model](#) [Packaging Specification 31910002-PK-000 \(PDF\)](#)  
[Drawing \(PDF\)](#) [Packaging Specification PK-3191-001-001 \(PDF\)](#)  
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**  
CSA LR19980  
UL E29179


**General**  
Product Family Crimp Housings  
Series [3191](#)  
Application Power, Wire-to-Wire  
Comments Polarized to Mating Part, with Mounting Ears  
Overview [Standard .093" Pin and Socket Connectors](#)  
Product Name Standard .093"  
UPC 800753872455

**Physical**  
Breakaway No  
Circuits (maximum) 1  
Color - Resin Natural  
Flammability 94V-0  
Gender Plug  
Glow-Wire Capable No  
Keying to Mating Part None  
Lock to Mating Part Yes  
Material - Resin Nylon  
Net Weight 1467.001/mg  
Number of Rows 1  
Packaging Type Bag  
Panel Mount Yes  
Pitch - Mating Interface N/A  
Polarized to Mating Part Yes  
Stackable No  
Temperature Range - Operating -40° to +105°C

**Electrical**  
Current - Maximum per Contact 12.0A

**Material Info**  
Engineering Number 3191-1P-201

**Reference - Drawing Numbers**  
Packaging Specification 31910002-PK-000, PK-3191-001-001  
Sales Drawing SD-3191-1X-001



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

|                 |               |
|-----------------|---------------|
| China ROHS      | Green Image   |
| ELV             | Not Relevant  |
| RoHS Phthalates | Not Contained |

**Search Parts in this Series**

[3191 Series](#)

**Mates With**

Standard .093" Receptacle Housing  
[19091016](#) , [19091019](#)

**Use With**

Standard .093" Female Crimp Terminals  
[1189](#) , [1381](#) , [1433](#) , [4550](#) . Standard .093"  
Male Crimp Terminals [1190](#) , [1380](#) , [1434](#) ,  
[1973](#) , [42138](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19-09-2017](#)