

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:0040130853

Status:Active

Description:MiniFit Term Crp Male Bs Au

General	
Product Family	Crimp Terminals
Series	5558
Crimp Quality Equipment	Yes
UPC	800753839915
Material Info	
Engineering Number	5558GS7
Reference - Drawing Numbers	
Application Specification	55560001-AS-000
Packaging Specification	55580001-PK-000
Product Specification	55560002-PS-CH-000, 55560002-PS-ES-000, 55560002-PS-SK-000, PS-5556-001-001, PS-5556-002-001
Sales Drawing	SD-5558-002-001
Test Summary	55560010-TS-000, TS-5556-002-001

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

5558 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extraction Tool for Mini-Fit Jr. Terminals	11030044
FineAdjust Applicator for Mini-Fit Double Crimp Applications Using Two 22 AWG Wires	2037026300
PremiumGrade Hand Crimp Tool for Mini-Fit Jr. Male and Female Terminals, 18-24 AWG	638190901
FineAdjust Applicator for 18-20 AWG and 18-24 AWG Wires with Insulation Diameter 1.90-2.30mm	639015600
FineAdjust Applicator for Insulation OD 1.40-1.70mm - 18-24 AWG	639023900
FineAdjust Applicator for Insulation OD 2.50-2.95mm Optimized for 18 AWG Only	639024800

FineAdjust Applicator	<u>639024900</u>
for Insulation OD	
2.30-2.60mm - 18-24	
AWG	
FineAdjust Applicator	<u>639047800</u>
for Insulation OD	
2.50-2.95mm, 18-24	
AWG	
FineAdjust Applicator	<u>639048000</u>
for Insulation OD	
1.65-2.05mm, 18-24	
AWG	
T2 Terminator	<u>639115600</u>
for insulation OD	
1.90-2.30mm - 18-24	
AWG	
T2 Terminator	<u>639123900</u>
for insulation OD	
1.40-1.70mm - 18-24	
AWG	
T2 Terminator	<u>639124800</u>
for insulation OD	
2.50-2.95mm	
optimized for 18	
AWG only	
T2 Terminator	<u>639124900</u>
for insulation OD	
2.30-2.60mm - 18-24	
AWG	
T2 Terminator	<u>639147800</u>
for Mini-Fit Crimp	
Terminals, 18-24	
AWG with Large	
Insulation ODs	
T2 Terminator	<u>639148000</u>
for Mini-Fit Crimp	
Terminals, 18-24	
AWG with Smaller	
Insulation ODs	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[40-13-0853](#)