


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0050579225](#)
Status: **Active**
Overview: [SL Modular Connectors](#)
Description: SL Crimp Housing, Single Row, Version C, Front Ribs, 25 Circuits, Black



Series image - Reference only

Documents:
[3D Model](#)
[3D Model \(PDF\)](#)
[Drawing \(PDF\)](#)
[Product Specification PS-70058-001 \(PDF\)](#)
[Product Specification PS-70400-001 \(PDF\)](#)
[Product Specification PS-71851-001 \(PDF\)](#)
[Packaging Specification PK-70066-100-001 \(PDF\)](#)
[Test Summary TS-70058-001-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
CSA LR19980
UL E29179

General
Product Family Crimp Housings
Series [70066](#)
Application Signal, Wire-to-Board
Comments Version C
Overview [SL Modular Connectors](#)
Product Name SL
UPC 800753784871

Physical
Circuits (maximum) 25
Color - Resin Black
Flammability 94V-0
Gender Receptacle
Glow-Wire Capable No
Keying to Mating Part Yes
Lock to Mating Part No
Material - Resin Polyester Alloy
Net Weight 0.178/g
Number of Rows 1
Packaging Type Bag
Panel Mount No
Pitch - Mating Interface 2.54mm
Stackable No
Temperature Range - Operating -40° to +105°C

Solder Process Data
Lead-freeProcess Capability N/A

Material Info
Engineering Number 70066-0094

Reference - Drawing Numbers
Packaging Specification PK-70066-100-001
Product Specification PS-70058-001, PS-70400-001, PS-71851-001
Sales Drawing SD-70066-0071-0094-001
Test Summary TS-70058-001-001

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
D(2021)4569-DC (8
July 2021)
Halogen-Free
Status
Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[70066](#) Series

Mates With
[70543](#) , [70545](#) , [70553](#) , [70555](#) , [70541](#) ,
[70551](#) , [70634](#) , [74099](#)

Use With
SL Crimp Terminal [70058](#) , [71851](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

50-57-9225