


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0134210008
Status: Active
Overview: Asset Tracking Solutions
Description: Alien Enterprise 4-port Fixed RFID Reader with Multi-Reader Management, 8 Additional Readers Supported, 920-925 MHz, for China and Singapore



Series image - Reference only

Documents:
[Datasheet \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	RFID Products
Series	13421
Comments	Includes Reader ONLY. No PoE/DC Power Supply Included.
Component Type	Fixed RFID Reader
Kit Option	Reader Only
LAN Protocols	TCP/IP,NTP,DNS,DHCP,SNMP
Market	China, Singapore
More Detailed Tech Information	For detailed product and compliance certification information, please visit https://www.alientechnology.com/download/alr-f800-x-documents/?wpdmdl=8100&ind=MTU2MjA4NjY5M3dwZG1fQUxSLUY4MDAtWCAoMjA0OCCwN0xMSUoGRmVhcnVl Alien Datasheet.
Overview	Asset Tracking Solutions
Product Name	Alien
RFID Standard	EPC C1 Gen 2,ISO 18000-6c
Reader Protocols	ARP,LLRP
Type	Enterprise w/Multi-Reader Mgmt
UPC	193264421565
Physical	
Additional Readers Supported	Up to 8
Antennas	Up to 4 Supported
Communications	LAN TCP/IP (RJ-45), RS-232 (DB-9 F), USB Console, USB Host
Dimensions	202.00 x 191.00 x 28.00mm
General Purpose I/O	4 in / 8 out (Isolated)
Memory	1 GB RAM,2 GB Flash
Operating System	Linux
Packaging Type	Carton
Software SDK	Java,.NET,Ruby APIs
Temperature Range - Operating	-20° to +50°C
Electrical	
Frequency	920-925 MHz
Max Conductive RF Power (dBm)	30.7
Power Source	PoE,AC/DC Power Converter
Material Info	
Engineering Number	F800-CHN-X2-RDRONL

EU ELV Not Reviewed	
EU RoHS Not Reviewed	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Reviewed	
For more information please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
13421 Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

13421-0008