

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0151660392

Status:

Active

Overview:

Description:

0.50mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 152.00mm Cable Length, Tin (Sn) Plating, 36 Circuits

|                               |                                    |
|-------------------------------|------------------------------------|
| General                       |                                    |
| Product Family                | Cable                              |
| Series                        | 15166                              |
| Comments                      | Contacts on opposite sides, Type D |
| Crimp Quality Equipment       | Yes                                |
| Overview                      | premo flex                         |
| Product Name                  | Premo-Flex FFC Jumper              |
| UPC                           | 884982848900                       |
| Physical                      |                                    |
| Cable Length                  | 152.00mm                           |
| Circuits (Loaded)             | 36                                 |
| Contact Layout Type           | D (opposite side)                  |
| Material - Plating Mating     | Tin                                |
| Net Weight                    | 1.000/g                            |
| Packaging Type                | Bag                                |
| Pitch - Mating Interface      | 0.50mm                             |
| Temperature Range - Operating | -40° to +105°C                     |
| Wire Size AWG                 | N/A                                |
| Wire/Cable Type               | Flat Flex Cable                    |
| Electrical                    |                                    |
| Current - Maximum per Contact | 0.5A                               |
| Voltage - Maximum             | 60V AC                             |
| Material Info                 |                                    |
| Reference - Drawing Numbers   |                                    |
| Product Specification         | PS-15166-001-001                   |
| Sales Drawing                 | SD-15166-001-001                   |

|                                                               |               |
|---------------------------------------------------------------|---------------|
| EU ELV                                                        |               |
| Not Relevant                                                  |               |
| EU RoHS                                                       | China RoHS    |
| Compliant                                                     |               |
| REACH SVHC                                                    |               |
| Not Reviewed                                                  |               |
| Halogen-Free                                                  |               |
| Status                                                        |               |
| Not Reviewed                                                  |               |
| For more information, please visit <a href="#">Contact US</a> |               |
| China ROHS                                                    | Green Image   |
| ELV                                                           | Not Relevant  |
| RoHS Phthalates                                               | Not Contained |

Search Parts in this Series

15166 Series

Mates With

Easy-On FFC/FPC Connector: . [541043633](#) , [541323633](#) , [525593633](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

15166-0392