

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0151680191

Status:

Active

Overview:

Description:

1.25mm Pitch Premo-Flex FFC Jumper, Same Side Contacts (Type A), 51.00mm Cable Length, Tin (Sn) Plating, 14 Circuits

|                         |                                   |
|-------------------------|-----------------------------------|
| General                 |                                   |
| Product Family          | Cable                             |
| Series                  | 15168                             |
| Comments                | Contacts on the same side, Type A |
| Crimp Quality Equipment | Yes                               |
| Overview                | premo flex                        |
| Product Name            | Premo-Flex FFC Jumper             |
| UPC                     | 884982856011                      |

|                               |                 |
|-------------------------------|-----------------|
| Physical                      |                 |
| Cable Length                  | 51.00mm         |
| Circuits (Loaded)             | 14              |
| Contact Layout Type           | A (same side)   |
| Material - Plating Mating     | Tin             |
| Net Weight                    | 1.000/g         |
| Packaging Type                | Bag             |
| Pitch - Mating Interface      | 1.25mm          |
| Temperature Range - Operating | -40° to +105°C  |
| Wire Size AWG                 | N/A             |
| Wire/Cable Type               | Flat Flex Cable |

|                               |        |
|-------------------------------|--------|
| Electrical                    |        |
| Current - Maximum per Contact | 1.4A   |
| Voltage - Maximum             | 60V AC |

Material Info

|                             |                  |
|-----------------------------|------------------|
| Reference - Drawing Numbers |                  |
| Product Specification       | PS-15168-001-001 |
| Sales Drawing               | SD-15168-001-001 |

EU ELV  
Not Relevant

|                            |            |
|----------------------------|------------|
| EU RoHS<br>Compliant       | China RoHS |
| REACH SVHC<br>Not Reviewed |            |
| Halogen-Free<br>Status     |            |
| Not Reviewed               |            |

For more information, please visit [Contact US](#)

|                 |               |
|-----------------|---------------|
| China ROHS      | Green Image   |
| ELV             | Not Relevant  |
| RoHS Phthalates | Not Contained |

Search Parts in this Series  
15168 Series

Mates With  
<a href="http://www.molex.com/product/ffc">Molex FFC – FPC connector</a>. Be sure to match like plating.

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[15168-0191](#)