

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190080038

Status:

Active

Overview:

Standard Quick-Disconnect Terminals

Description:

Flag Krimptite Quick Disconnect, Female, for 12-14 (3.30-2.00mm²) Wire, Box, Tab 6.35 x 0.81mm

- Documents:
- 3D Model

Product Specification PS-19902-011-001 (PDF)
- Drawing (PDF)

Product Specification PS-19902-013-001 (PDF)
- 3D Model (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification PS-19902-005-001 (PDF)

General

Product Family

Quick Disconnects

Series

19008

Comments

Fits Hermetic Tabs

Crimp Quality Equipment

Yes

Insulated

No

Overview

Standard Quick-Disconnect Terminals

Product Name

Krimptite

Type

Quick Disconnect

UPC

800755046762

Physical

Barrel Type

Closed

Gender

Female

Glow-Wire Capable

No

Insulation

None

Lock to Mating Part

None

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Net Weight

0.785/g

Orientation

Flag

Packaging Type

Bag

Polarized to Mating Part

No

Tab Thickness

0.81mm

Tab Width

6.35mm

Temperature Range - Operating

Per Wire Specification

Termination Interface: Style

Crimp or Compression

Wire Size AWG

12, 14

Electrical

Voltage - Maximum

Per Wire Specification

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Engineering Number

B-175


Reference - Drawing Numbers

Product Specification

PS-19902-005-001, PS-19902-011-001, PS-19902-013-001

Sales Drawing

SD-19008-009-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2021)4569-DC (8

July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19008 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Hand Crimp Tool

640030700

This document was generated on 09/14/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19008-0038](#)