

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0190090016](#)
Status: **Active**
Overview: [Standard Quick-Disconnect Terminals](#)
Description: [VibraKrimp Quick Disconnect Flag, Female, for 14-16 AWG Wire, Metal Strip Carrier](#)

Documents:
[3D Model](#) [Product Specification PS-19902-011-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [Packaging Specification PK-19009-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-19902-005-001 \(PDF\)](#)

Agency Certification
CSA LR18689
UL E79133


General
Product Family Quick Disconnects
Series [19009](#)
Comments Wire Grip
Crimp Quality Equipment Yes
Insulated No
Overview [Standard Quick-Disconnect Terminals](#)
Product Name VibraKrimp
Type Quick Disconnect
UPC 800755046915

Physical
Barrel Type Closed
Gender Female
Glow-Wire Capable No
Insulation None
Lock to Mating Part None
Material - Metal Brass
Material - Plating Mating Tin
Material - Plating Termination Tin
Net Weight 0.763/g
Orientation Flag
Packaging Type Reel
Polarized to Mating Part No
Tab Thickness 0.81mm
Tab Width 6.35mm
Temperature Range - Operating Per Wire Specification
Wire Insulation Diameter 3.68mm
Wire Size AWG 14, 16
Wire Size mm² 1.30-2.00

Electrical
Voltage - Maximum Per Wire Specification

Material Info
Engineering Number BBZ-4169

Reference - Drawing Numbers
Packaging Specification PK-19009-001-001
Product Specification PS-19902-005-001, PS-19902-011-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
D(2021)4569-DC (8
July 2021)
Halogen-Free
Status
Low-Halogen
For more information, please visit [Contact US](#)

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series
[19009 Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.
Global

Description	Product #
Mini-Mac Applicator	638027700
Rear Feed	

This document was generated on 08/31/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19009-0016](#)