

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190380001

Status:

Active

Overview:

Snap Plugs and Receptacles

Description:

InsulKrimp Snap Plug Receptacle, for 18-22 AWG Wire, PVC, Fits Male Plug Diameter 3.96mm

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-19902-011-001 (PDF)

Product Specification PS-19902-013-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

UL

LR18689

E152602

General

Product Family

Series

Comments

Crimp Quality Equipment

Insulated

Overview

Product Name

Type

UPC

Quick Disconnects

19038

Fits Male Plug size 3.96mm

Yes

Fully

Snap Plugs and Receptacles

InsulKrimp

Snap Receptacle

800753048621

Physical

Barrel Type

Color - Resin

Flammability

Gender

Glow-Wire Capable

Insulation

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Plating Termination

Material - Resin

Net Weight

Orientation

Packaging Type

Plating min - Mating

Plating min - Termination

Tab Thickness

Tab Width

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Closed

Red

94V-0

Female

No

PVC

None

Brass

Tin

Tin

PVC

1.041/g

Straight

Bag

4.064µm

4.064µm

N/A

N/A

Crimp or Compression

3.25mm max.

18, 20, 22

Electrical

Voltage - Maximum

600V

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Engineering Number

BRA-2156



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2021)4569-DC (8

July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19038 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Hand Crimp Tool	640012300
Crimp Head for the AT-200 Pneumatic Hand Tool	640052300

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-19902-011-001, PS-19902-013-001

SD-19038-001-001

This document was generated on 08/31/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19038-0001](#)