

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190380006

Status:

Active

Overview:

Snap Plugs and Receptacles

Description:

InsulKrimp Snap Plug Receptacle for 18-22 AWG Wire, Nylon, Fits Male Plug Diameter 4.57mm

Documents:

3D Model

Product Specification PS-19902-011-001 (PDF)

3D Model (PDF)

Product Specification PS-19902-013-001 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR18689

UL

E152602

General

Product Family

Quick Disconnects

Series

19038

Comments

Fits Male Plug Dia. 4.57mm

Crimp Quality Equipment

Yes

Insulated

Fully

Overview

Snap Plugs and Receptacles

Product Name

InsulKrimp

Type

Snap Receptacle

UPC

800753048706

Physical

Barrel Type

Closed

Color - Resin

Red

Flammability

94V-2

Gender

Female

Glow-Wire Capable

No

Insulation

Nylon (PA)

Lock to Mating Part

None

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

Nylon

Net Weight

1.119/g

Orientation

Straight

Packaging Type

Bag

Plating min - Mating

2.540µm

Plating min - Termination

2.540µm

Tab Thickness

N/A

Tab Width

N/A

Termination Interface: Style

Crimp or Compression

Wire Insulation Diameter

3.25mm max.

Wire Size AWG

18, 20, 22

Electrical

Voltage - Maximum

600V

Material Info

Engineering Number

BRA-2180N

Reference - Drawing Numbers

Product Specification

PS-19902-011-001, PS-19902-013-001

Sales Drawing

SD-19038-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per

-ED/88/2018 (15

January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19038 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool	640012300
Crimp Head for the AT-200 Pneumatic Hand Tool	640052300

This document was generated on 07/31/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19038-0006](#)