

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190380011

Status:

Active

Overview:

Snap Plugs and Receptacles

Description:

InsulKrimp Snap Plug Receptacle for 14-16 AWG Wire, PVC, Fits Male Plug Diameter 4.57mm

Documents:

Drawing (PDF)

3D Model (PDF)

3D Model

Product Specification PS-19902-011-001 (PDF)

Product Specification PS-19902-013-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA		LR18689
UL		E152602
General		
Product Family		Quick Disconnects
Series		19038
Comments		Fits Male Plug Dia. 4.57mm
Crimp Quality Equipment		Yes
Insulated		Fully
Overview		Snap Plugs and Receptacles
Product Name		InsulKrimp
Type		Snap Receptacle
UPC		800753048782
Physical		
Barrel Type		Closed
Color - Resin		Blue
Flammability		94V-0
Gender		Female
Glow-Wire Capable		No
Insulation		PVC
Lock to Mating Part		None
Material - Metal		Brass
Material - Plating Mating		Tin
Material - Plating Termination		Tin
Material - Resin		PVC
Net Weight		1.248/g
Orientation		Straight
Packaging Type		Bag
Tab Thickness		N/A
Tab Width		N/A
Termination Interface: Style		Crimp or Compression
Wire Insulation Diameter		3.81mm max.
Wire Size AWG		14, 16
Wire Size mm²		1.00-2.50
Electrical		
Voltage - Maximum		600V
Solder Process Data		
Lead-freeProcess Capability		N/A
Material Info		
Engineering Number		BRB-2180

Reference - Drawing Numbers



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

19038 Series

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
Hand Crimp Tool	640012100
Crimp Head for the AT-200 Pneumatic Hand Tool	640052100

This document was generated on 01/03/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19038-0011](#)