

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0190690205

Status:

Active

Overview:

Solderless Terminals

Description:

Krimptite Ring Tongue Terminal for 10-12 AWG Wire, Stud Size 8 (M4), Length 19.94mm

Documents:

Drawing (PDF)

3D Model (PDF)

3D Model

Product Specification PS-19902-011-001 (PDF)

Product Specification PS-19902-013-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

UL

LR18689

E32244

General

Product Family

Series

Crimp Quality Equipment

Overview

Product Name

Type

UPC

Ring and Spade Terminals

19069

Yes

Solderless Terminals

Krimptite

Ring

800753068148

Physical

Barrel Type

Insulation

Material - Plating Mating

Material - Plating Termination

Net Weight

Packaging Type

Plating min - Mating

Plating min - Termination

Stud Size

Termination Interface: Style

Wire Size AWG

Wire Size mm²

Closed

None

Tin

Tin

1.579/g

Bag

2.540µm

2.540µm

8 (M4)

Crimp or Compression

10, 12

4.00-6.00

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Engineering Number

C-128-08

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-19902-011-001, PS-19902-013-001

SD-19069-020-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

19069 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade	640030100
Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm² - 0.5mm²	
Crimp Head for the AT-200 Pneumatic Hand Tool	640070100
ServiceGrade Hand Crimp Tool - Ratchet	640160038

This document was generated on 10/12/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19069-0205](#)