

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [0190720051](#)  
**Status:** **Active**  
**Overview:** [Solderless Terminals](#)  
**Description:** VibraKrimp Ring Tongue Terminal 16 – 14 AWG for Stud Size 5/16" (M8), Length 31.27mm

**Documents:**  
[3D Model](#) [Product Specification PS-19902-011-001 \(PDF\)](#)  
[3D Model \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)


**Agency Certification**  
CSA LR18689  
UL E32244

**General**  
Product Family Ring and Spade Terminals  
Series [19072](#)  
Crimp Quality Equipment Yes  
Overview [Solderless Terminals](#)  
Product Name VibraKrimp  
Type Ring  
UPC 800753073937

**Physical**  
Barrel Type Closed  
Insulation None  
Material - Plating Mating Tin  
Net Weight 1.448/g  
Packaging Type Bag  
Plating min - Mating 2.540µm  
Plating min - Termination 2.540µm  
Stud Size 2 (M2)  
Wire Size AWG 14, 16

**Material Info**  
Engineering Number BB-418-56

**Reference - Drawing Numbers**  
Product Specification PS-19902-011-001, PS-19902-013-001  
Sales Drawing 190720046-000



Series image - Reference only

**EU ELV**  
**Not Relevant**

**EU RoHS** **China RoHS**  
**Compliant**  
**REACH SVHC**  
Not Contained Per -  
D(2021)4569-DC (8  
July 2021)  
**Halogen-Free**  
**Status**  
**Low-Halogen**  
For more information, please visit [Contact US](#)

China ROHS Green Image  
ELV Not Relevant  
RoHS Phthalates Not Contained

**Search Parts in this Series**  
[19072 Series](#)

**Application Tooling | [FAQ](#)**  
*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

| Global                                        |                           |
|-----------------------------------------------|---------------------------|
| Description                                   | Product #                 |
| Crimp Hand Tool                               | <a href="#">640016800</a> |
| Crimp Head for the AT-200 Pneumatic Hand Tool | <a href="#">640056800</a> |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19072-0051](#)