

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0191190007

Status:

Active

Overview:

Solderless Terminals

Description:

InsulKrimp Long Barrel Flanged Spade Terminal for 14-22 AWG Wire, Stud Size 8 (M4), Length 21.23mm

Documents:

- 3D Model

Product Specification PS-19902-011-001 (PDF)
- 3D Model (PDF)

Product Specification PS-19902-013-001 (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification PS-19902-009-001 (PDF)

Agency Certification

UL

E32244

General

Product Family

Series

Crimp Quality Equipment

Overview

Product Name

Type

UPC

Ring and Spade Terminals

19119

Yes

Solderless Terminals

InsulKrimp

Spade

800753094123

Physical

Barrel Type

Color - Resin

Flammability

Insulation

Material - Plating Mating

Net Weight

Packaging Type

Stud Size

Wire Insulation Diameter

Wire Size AWG

Wire Size mm²

Open

Red

94V-0

PVC

Tin

0.775/g

Bag

8 (M4)

3.68mm

14, 16, 18, 22

0.25-1.50

Material Info

Engineering Number

A-215-08X


Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-19902-009-001, PS-19902-011-001, PS-19902-013-001

SD-19119-003-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

19119 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade	640010100
Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 10-22 AWG and 6.0-0.5mm² (Rings, Spades, Hooks, Block Spades and Flanged Spades)	
Crimp Head for the AT-200 Pneumatic Hand Tool	640050100

ServiceGrade Hand 640160036
Crimp Tool for Field
Repair only, for
production use our
PremiumGrade Tool

This document was generated on 08/26/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19119-0007](#)