

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0191640015](#)
Status: **Active**
Overview: [Perma-Seal Terminals](#)
Description: Perma-Seal Male Quick Disconnect Tab for 18-22 AWG Wire, Tab Size 6.35 x 0.81mm, Bag

Documents:
[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
CSA LR18689
UL E79133

General
Product Family Quick Disconnects
Series [19164](#)
Crimp Quality Equipment Yes
Insulated Partial
Overview [Perma-Seal Terminals](#)
Product Name Perma-Seal
Type Quick Disconnect
UPC 800753113039

Physical
Barrel Type Closed
Color - Resin Red
Gender Male
Glow-Wire Capable No
Insulation NiAc
Lock to Mating Part None
Material - Metal Brass
Material - Plating Mating Zinc Chromate
Material - Plating Termination Zinc Chromate
Material - Resin Nylon
Net Weight 1.633/g
Orientation Straight
Packaging Type Bag
Plating min - Mating 5.080µm
Plating min - Termination 5.080µm
Tab Thickness 0.81mm
Tab Width 6.35mm
Temperature Range - Operating -55° to +125°C
Wire Insulation Diameter 3.81mm max.
Wire Size AWG 18, 20, 22

Electrical
Voltage - Maximum 600V

Material Info
Engineering Number SAA-9260

Reference - Drawing Numbers
Product Specification PS-19902-011-001, PS-19902-013-001
Sales Drawing SD-19164-038



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ECHA_01_2020 (16 January 2020)	
Halogen-Free Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[19164 Series](#)

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade Hand Crimp Tool	640014500
PremiumGrade Hand Crimp Tool for Industrial Terminals 14-22 AWG (see ATS)	640014700
Crimp Head for the AT-200 Pneumatic Hand Tool	640054500
Crimp Head for the AT-200 Pneumatic Hand Tool	640054700

This document was generated on 07/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

19164-0015