

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0192110005
Status: Active
Overview: Wire Pins
Description: Krimptite Wire Pin Terminal for 16-14 AWG Wire

Documents:
[Drawing \(PDF\)](#) [Product Specification PS-19902-013-001 \(PDF\)](#)
[Product Specification PS-19902-011-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
CSA LR18689
UL E32244

General
Product Family Crimp Terminals
Series 19211
Application Power, Wire-to-Component
Comments Pin Length 9.65mm
Crimp Quality Equipment Yes
Overview Wire Pins
Packaging Alternative 192110006 (Adhesive Tape on Reel)
Product Name Wire Pin
UPC 800755062052

Physical
Gender Male
Material - Metal Copper
Material - Plating Mating Tin
Net Weight 0.626/g
Packaging Type Bag
Plating min - Mating 1.016µm
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 2.26mm max.
Wire Size AWG 14, 16
Wire Size mm² N/A

Material Info
Engineering Number WP-1614

Reference - Drawing Numbers
Product Specification PS-19902-011-001, PS-19902-013-001
Sales Drawing SD-19211-002-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
D(2021)4569-DC (8
July 2021)
Halogen-Free
Status
Low-Halogen
For more information, please visit [Contact US](#)

China ROHS Green Image
ELV Not Relevant
RoHS Phthalates Not Contained

Search Parts in this Series
19211 Series

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade	640030100
Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm² - 0.5mm²	
Crimp Head for the AT-200 Pneumatic Hand Tool	640070100
ServiceGrade Hand Crimp Tool - Ratchet	640160038

This document was generated on 09/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

19211-0005