

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0192110001

Status:

Active

Overview:

Wire Pins

Description:

Krimptite Wire Pin Terminal for 12-10 AWG Wire

Documents:

Drawing (PDF)

Product Specification PS-19902-011-001 (PDF)

Product Specification PS-19902-013-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR18689

UL

E32244

General

Product Family

Crimp Terminals

Series

19211

Application

Power, Wire-to-Component

Comments

Pin Length 11.43mm

Crimp Quality Equipment

Yes

Overview

Wire Pins

Packaging Alternative

192110002 (Adhesive Tape on Reel)

Product Name

Wire Pin

UPC

800755061994

Physical

Gender

Male

Material - Metal

Copper

Material - Plating Mating

Tin

Net Weight

1.465/g

Packaging Type

Bag

Plating min - Mating

1.016µm

Termination Interface: Style

Crimp or Compression

Wire Insulation Diameter

3.45mm max.

Wire Size AWG

10, 12

Wire Size mm²

N/A

Material Info

Engineering Number

WP-1210

Reference - Drawing Numbers

Product Specification

PS-19902-011-001, PS-19902-013-001

Sales Drawing

SD-19211-002-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19211 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade	640030100
Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm² - 0.5mm²	
Crimp Head for the AT-200 Pneumatic Hand Tool	640070100
ServiceGrade Hand Crimp Tool - Ratchet	640160038

This document was generated on 08/25/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19211-0001](#)