

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0192130009**  
**Status:** **Active**  
**Overview:** Wire Pins  
**Description:** Avikrimp Wire Pin Terminal for 22-18 AWG Wire, Loose in bag

**Documents:**

3D Model Product Specification PS-19902-011-001 (PDF)  
3D Model (PDF) Product Specification PS-19902-013-001 (PDF)  
Drawing (PDF) RoHS Certificate of Compliance (PDF)

**Agency Certification**

CSA LR18689  
 UL E32244

**General**

Product Family Crimp Terminals  
 Series 19213  
 Application Power, Wire-to-Component  
 Comments Pin Length 9.91mm  
 Crimp Quality Equipment Yes  
 Overview Wire Pins  
 Packaging Alternative 192130010 (Adhesive Tape on Reel)  
 Product Name Wire Pin  
 UPC 800753053496

**Physical**


Flammability 94V-2  
 Gender Male  
 Material - Metal Copper  
 Material - Plating Mating Tin  
 Net Weight 0.845/g  
 Packaging Type Bag  
 Plating min - Mating 1.016µm  
 Termination Interface: Style Crimp or Compression  
 Wire Insulation Diameter 6.35mm max.  
 Wire Size AWG 18, 19, 20, 22  
 Wire Size mm<sup>2</sup> N/A

**Material Info**

Engineering Number WP-8218

**Reference - Drawing Numbers**

Product Specification PS-19902-011-001, PS-19902-013-001  
 Sales Drawing SD-19213-002-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 D(2021)4569-DC (8  
 July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

19213 Series

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

PremiumGrade 640010100

Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 10-22 AWG and 6.0-0.5mm<sup>2</sup> (Rings, Spades, Hooks, Block Spades and Flanged Spades)  
 Crimp Head for the AT-200 Pneumatic Hand Tool

640050100

ServiceGrade Hand 640160036  
Crimp Tool for Field  
Repair only, for  
production use our  
PremiumGrade Tool

This document was generated on 08/31/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19213-0009](#)