

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0192210244](#)
Status: **Active**
Overview:
Description: Compression Style Ring Tongue Terminal for 2/0 AWG Wire, Stud Size 3/8" (M9), Plated

Agency Certification

CSA LR18689
 UL E32244

General

Product Family Ring and Spade Terminals
 Series [19221](#)
 Comments Heavy Duty
 Crimp Quality Equipment Yes
 Overview [battery_cable_lugs](#)
 Product Name Battery Cable Lug
 Type Ring
 UPC 800753062436

Physical

Barrel Type Closed
 Insulation None
 Material - Plating Mating Tin
 Net Weight 21.283/g
 Packaging Type Bag
 Plating min - Mating 4.064µm
 Plating min - Termination 4.064µm
 Stud Size 3/8" (M9)
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter N/A
 Wire Size AWG 2/0

Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Engineering Number BCL-2038-PL

Reference - Drawing Numbers

Product Specification PS-19901-017-001, PS-19902-011-001,
 PS-19902-013-001, PS-19902-017-001
 Sales Drawing SD-19221-011-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2020)9139-DC (19
 Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[19221](#) Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description **Product #**

Hand Crimp Tool for Eyelet Style Copper Lug Terminals 8-4/0 AWG [192840034](#)
 Manual Putt Pump Hydraulic System, Die set required [192860117](#)
 Die Set (large) for the HHLS Hydraulic Crimper [192900012](#)
 Manual tool for Crimping non-insulated 8AWG thru 4/0 Terminals [192940008](#)
 Hydraulic Dieless Crimping Tool [638161700](#)
 Square "Din" Style Die Set for BCL and VersaKrimp Un-insulated Ring Tongue Terminals and Splices, 1/0 and 2/0 AWG [640038070](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19221-0244](#)