



CENTERLINE OF PIN AT TIP
NOT TO VARY FROM
CENTERLINE OF PIN AT DATUM -D-
BY MORE THAN .005 IN ANY DIRECTION

	6	HI
	5	H
	4	H
	3	H
	2	H
	1	HI
MFG.	SH.	REV.

LTR. REVISIONS		LTR. REVISIONS		REL 0588/0604 UCR2002-0752 03/11/02 SAMIEC		DIMENSIONS SHOWN METRIC/INCH UNLESS OTHERWISE SPECIFIED TOLERANCES ANGULAR ± 1/2°		TITLE FLAT HEADER ASS'Y 156 Q BENT SQ PINS, W/O PEG 41772 SERIES DRAWING		REVISIONS ONLY ON CAD SYSTEM	
		H		REV TO WW SPEC UCR2002-0077 7/25/01 SAMIEC		INCH METRIC 3 PLACE ± ± 2 PLACE ± ± 1 PLACE ± ±		MOLEX INCORPORATED LISLE, ILL. 60832 U.S.A.		SHEET NO. DATE 1 OF 6 09/09/81	
		G3		REL 0574/0587 UCR2001-0262 9-19-00 SAMIEC		DRAW. BY CHK'D BY SAMIEC PATEL APP'D. LENZ SCALE :		PART NO. DWG. NO. SEE CHART SD A-41772		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.	
LTR. REVISIONS		LTR. REVISIONS						FILE NAME 541772X1		DIV. SIZE C C	

I3		I2		I1		I0		9		8		7		6		41772		4		3		2		1			
ENG. NO.		HEADER NO.		PIN NO.		PLATING		DIM. L		DIM. X		DIM. G GOLD		DIM. Y		DIM. Z		DIM. T TIN		DIM. W		NO OF CKTS		VOID CKTS		PACKAGING	
A-41772-0368/0377		41770-0009/0018		2161-16(102)		102		(25.40) .1000		(14.86) .585		() N/A		(4.95) .195		(3.56) .140		() OVERALL		90°		9-18		9		BULK PER PK-41772-002	
A-41772-0378/0394		41770-0002/0018		2161--56(102) *		102		(17.86) .703		(5.94) .234		() N/A		(4.90) .193		(4.45) .175		() OVERALL		90°		2-18				BULK PER PK-41772-001	
A-41772-0412/0428		41770-0002/0018		2161-63(102) *		102		(24.38) .960		(15.06) .593		() N/A		(2.71) .107		(4.06) .160		() OVERALL		90°		2-18				BULK PER PK-41772-001	
A-41772-0429/0445		41770-0002/0018		2161-67(102) *		102		(18.69) .736		(10.48) .413		() N/A		(2.71) .107		(2.92) .115		() OVERALL		90°		2-18				BULK PER PK-41772-001	
A-41772-0446/0462		41770-0002/0018		2161-21(501)		501		(28.57) .1125		(17.60) .693		() OVERALL		(4.95) .195		(3.99) .157		() N/A		90°		2-18				BULK PER PK-41772-002	
A-41772-0531/0547		41770-0002/0018		2161-62(102)		102		(24.89) .980		(14.86) .585		() N/A		(4.95) .195		(3.05) .120		() OVERALL		90°		2-18				BULK PER PK-41772-002	
H																											
▪ ON ASSEMBLIES A-41772-0378 / -0445 THE PIN BEND RADIUS IS TO BE .045 R																											
G																											
F																											
E																											
D																											
C																											
B																											
A																											
41772																											

A-41772-0368/0377				A-41772-0378/0394				A-41772-0412/0428				A-41772-0429/0445				A-41772-0446/0462				A-41772-0531/0547													
EDP NO.		ENG. NO.		NO OF CKTS		EDP NO.		ENG. NO.		NO OF CKTS		EDP NO.		ENG. NO.		NO OF CKTS		EDP NO.		ENG. NO.		NO OF CKTS		EDP NO.		ENG. NO.		NO OF CKTS					
				2		26-60-3029		A-41772-0378		2		27-60-3020		A-41772-0412		2		A-41772-0429		2		27-60-3022		A-41772-0446		2		41772-0531		A-41772-0531		2	
				3		26-60-3039		A-41772-0379		3				A-41772-0413		3		A-41772-0430		3		27-60-3032		A-41772-0447		3		41772-0532		A-41772-0532		3	
				4		26-60-3049		A-41772-0380		4				A-41772-0414		4		A-41772-0431		4		27-60-3042		A-41772-0448		4		41772-0533		A-41772-0533		4	
				5		26-60-3059		A-41772-0381		5				A-41772-0415		5		A-41772-0432		5		27-60-3052		A-41772-0449		5		41772-0534		A-41772-0534		5	
				6		26-60-3069		A-41772-0382		6				A-41772-0416		6		27-60-3061		6		27-60-3062		A-41772-0450		6		41772-0535		A-41772-0535		6	
				7		26-60-3079		A-41772-0383		7		27-60-3070		A-41772-0417		7		27-60-3071		7		27-60-3072		A-41772-0451		7		41772-0536		A-41772-0536		7	
				8		26-60-3089		A-41772-0384		8				A-41772-0418		8				8		27-60-3082		A-41772-0452		8		41772-0537		A-41772-0537		8	
		A-41772-0368		9		26-60-3099		A-41772-0385		9				A-41772-0419		9				9		27-60-3092		A-41772-0453		9		41772-0538		A-41772-0538		9	
		A-41772-0369		10		26-60-3109		A-41772-0386		10				A-41772-0420		10				10		27-60-3102		A-41772-0454		10		41772-0539		A-41772-0539		10	
		A-41772-0370		11		26-60-3119		A-41772-0387		11				A-41772-0421		11				11		27-60-3112		A-41772-0455		11		41772-0540		A-41772-0540		11	
		26-62-3125		A-41772-0371		12		26-60-3129		A-41772-0388		12		A-41772-0422		12				12		27-60-3122		A-41772-0456		12		41772-0541		A-41772-0541		12	
				A-41772-0372		13		26-60-3139		A-41772-0389		13		A-41772-0423		13				13		27-60-3132		A-41772-0457		13		41772-0542		A-41772-0542		13	
				A-41772-0373		14		26-60-3149		A-41772-0390		14		A-41772-0424		14				14		27-60-3142		A-41772-0458		14		41772-0543		A-41772-0543		14	
				A-41772-0374		15		26-60-3159		A-41772-0391		15		A-41772-0425		15				15		27-60-3152		A-41772-0459		15		41772-0544		A-41772-0544		15	
				A-41772-0375		16		26-60-3169		A-41772-0392		16		A-41772-0426		16				16		27-60-3162		A-41772-0460		16		41772-0545		A-41772-0545		16	
				A-41772-0376		17		26-60-3179		A-41772-0393		17		A-41772-0427		17				17		27-60-3172		A-41772-0461		17		41772-0546		A-41772-0546		17	
				A-41772-0377		18		26-60-3189		A-41772-0394		18		A-41772-0428		18				18		27-60-3182		A-41772-0462		18		41772-0547		A-41772-0547		18	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[26-60-3149](#)