

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0313862002

Status:

Active

Overview:

MX123 Sealed Connection System

Description:

2.54mm Pitch, MX123 Header, 56 Circuits Shrouded Assembly, Qty(56) 0.64mm Square Signal Pins, Harness Side Key Code H, Gray (Au Mate Side Finish)



Series image - Reference only

Documents:

3D Model	Application Specification AS-31386-200-001 (PDF)
Drawing (PDF)	Packaging Specification PK-31301-916-001 (PDF)
3D Model (PDF)	Test Summary TS-31386-1719-001 (PDF)
Product Specification PS-31386-200-001 (PDF)	Datasheet (PDF)
Product Specification PS-34566-0000-001 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	PCB Headers
Series	31386
Application	Automotive, Power, Wire-to-Board
Overview	MX123 Sealed Connection System
Product Name	MX123
UPC	883906922047

Physical

Breakaway	No
Circuits (Loaded)	56
Circuits (maximum)	56
Color - Resin	Gray
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	17.698/g
Number of Rows	4
Orientation	Vertical
PC Tail Length	6.50mm
PCB Locator	No
PCB Retention	None
Packaging Type	Carton
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Yes
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +125°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	11.0A
Voltage - Maximum	500V

Material Info

Reference - Drawing Numbers

Application Specification	AS-31386-200-001
---------------------------	------------------

EU ELV

Compliant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[31386](#) Series

Mates With

MX123 Female Harness Connector
Assembly [34576](#)

Use With

[33467](#) MX64 Female Terminals Au

Packaging Specification
Product Specification
Sales Drawing
Test Summary

PK-31301-916-001
PS-31386-200-001, PS-34566-0000-001
SD-31386-056-000, SD-31386-156-000
TS-31386-1719-001

This document was generated on 07/27/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[31386-2002](#)