

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0314022710

Status:


Active

Overview:

MX64 Sealed Connectors

Description:

2.54mm MX64 Sealed Single Row Crimp Housing, GET Terminal, Black, 2 Circuits, Key D, with CPA Lock



- Documents:
- 3D Model

Application Specification AS-31402-000-001 (PDF)
- Drawing (PDF)

Packaging Specification PK-31300-256-001 (PDF)
- 3D Model (PDF)

Test Summary TS-31402-001-1X2-001 (PDF)
- Product Specification PS-31402-000-001 (PDF)

RoHS Certificate of Compliance (PDF)
- Application Specification 314020000-000 (PDF)

General	
Product Family	Crimp Housings
Series	31402
Application	Power, Wire-to-Board
More Detailed Tech Information	http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications-Partnership
Overview	MX64 Sealed Connectors
Polarization	D
Product Name	MX64
UPC	822348656660
Physical	
Circuits (maximum)	2
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	4.710/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +125°C
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	CVP-314022710
Reference - Drawing Numbers	
Application Specification	314020000-000, AS-31402-000-001
Packaging Specification	PK-31300-256-001
Product Specification	PS-31402-000-001
Sales Drawing	SD-31402-211-001
Test Summary	TS-31402-001-1X2-001

EU ELV

Compliant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Compliant

Not Contained

Search Parts in this Series

31402 Series

Mates With

Sensors, Other USCAR Interfaces

Use With

Molex GET Terminals [34230](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[31402-2710](#)