

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0313721000](#)
Status: **Active**
Overview: [Stac64 Single, Multi-Pocket and Hybrid Header System](#)
Description: [Stac64 Hybrid Receptacle Assembly, 10 Circuit, Black, Polarization A, without CPA](#)

Documents:

3D Model	Application Specification AS-31372-100-001 (PDF)
Drawing (PDF)	Application Specification AS-34729-020-001 (PDF)
3D Model (PDF)	Packaging Specification PK-31300-931-001 (PDF)
Product Specification PS-31372-100-001 (PDF)	Brochure (PDF)
Application Specification 347290200-AS-CH-000 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Housings
Series	31372
Application	Automotive, Power, Wire-to-Board
Comments	Polarization A, 6 x 1.50 and 4 x 2.8
Overview	Stac64 Single, Multi-Pocket and Hybrid Header System
Product Name	Stac64
UPC	822348054497

Physical

Circuits (maximum)	10
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene
Net Weight	8.060/g
Number of Rows	2
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm, 5.25mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +100°C

Electrical

Current - Maximum per Contact	22.0A, 30.0A
-------------------------------	--------------

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	347290200-AS-CH-000, AS-31372-100-001, AS-34729-020-001
Packaging Specification	PK-31300-931-001
Product Specification	PS-31372-100-001
Sales Drawing	313729000-000



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Missing Compliance Data

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[31372 Series](#)

Mates With

[Stac64 Right Angle Assembly 34696](#) .
[Stac64 Vertical Assembly 34695](#)

Use With

[MX150 Terminal 33012](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[31372-1000](#)