

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0313862021

Status:

Active

Overview:

MX123 Sealed Connection System

Description:

2.54mm Pitch, MX123 Header, 56 Circuits Shrouded Assembly, Qty(56) 0.64mm Square Signal Pins, Harness Side Key Code H, Gray (Ag Mate Side Finish)



Documents:	
3D Model	Packaging Specification PK-31301-916-001 (PDF)
Drawing (PDF)	Test Summary TS-31386-1719-001 (PDF)
3D Model (PDF)	Datasheet (PDF)
Product Specification PS-31386-200-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-31386-200-001 (PDF)	

General	
Product Family	PCB Headers
Series	31386
Application	Automotive, Power, Wire-to-Board
Overview	MX123 Sealed Connection System
Product Name	MX123
UPC	884982917064
Physical	
Breakaway	No
Circuits (Loaded)	56
Circuits (maximum)	56
Color - Resin	Gray
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Plating Mating	Silver
Material - Plating Termination	Tin
Net Weight	18.027/g
Number of Rows	4
Orientation	Vertical
PC Tail Length	6.50mm
PCB Locator	No
PCB Retention	None
Packaging Type	Carton
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Yes
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +125°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	11.0A
Voltage - Maximum	500V
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-31386-200-001

EU ELV Compliant	
EU RoHS Compliant	China RoHS
REACH SVHC Not Reviewed	
Halogen-Free Status Not Relevant	
For more information, please visit Contact US	
China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
31386 Series

Mates With
MX123 Female Harness Connector
Assembly 34576

Use With
34736 MX64 Female Terminals Ag

Packaging Specification
Product Specification
Sales Drawing
Test Summary

PK-31301-916-001
PS-31386-200-001
SD-31386-056-000, SD-31386-156-000
TS-31386-1719-001

This document was generated on 07/29/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[31386-2021](#)