

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0314032200

Status:

Active

Overview:

MX64 Sealed Connectors

Description:

2.54mm MX64 Sealed Single Row Crimp Housing, MX64 Terminal, Gray, 2 Circuits, Key B, without CPA Lock



Series image - Reference only

- Documents:
- 3D Model

Application Specification AS-31402-000-001 (PDF)
- Drawing (PDF)

Packaging Specification PK-31300-256-001 (PDF)
- 3D Model (PDF)

Test Summary TS-31402-001-1X2-001 (PDF)
- Product Specification PS-31402-000-001 (PDF)

RoHS Certificate of Compliance (PDF)
- Application Specification 314020000-000 (PDF)

General	
Product Family	Crimp Housings
Series	31403
Application	Power, Wire-to-Board
More Detailed Tech Information	http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications-Partnership
Overview	MX64 Sealed Connectors
Polarization	B
Product Name	MX64
UPC	883906411701
Physical	
Circuits (maximum)	2
Color - Resin	Gray
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	PBT
Net Weight	4.330/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +125°C
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Engineering Number	CVP-314032200
Reference - Drawing Numbers	
Application Specification	314020000-000, AS-31402-000-001
Packaging Specification	PK-31300-256-001
Product Specification	PS-31402-000-001
Sales Drawing	SD-31402-211-001
Test Summary	TS-31402-001-1X2-001

EU ELV

Compliant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -

D(2021)4569-DC (8

July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series
31403 Series

Mates With
Sensors, Other USCAR Interfaces

Use With
Molex MX64 Terminals 33467 , 33468

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

31403-2200