

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0340801106

Status:

Active

Overview:

MX150 Sealed and Unsealed Connector System

Description:

MX150 Cable Seal Male Terminal, Gold Plating, 22 AWG, Left Reel Payoff



Series image - Reference only

Documents:

- Drawing (PDF)

Product Specification PS-34083-002-001 (PDF)

Application Specification AS-34080-001-001 (PDF)

Packaging Specification 313025040-000 (PDF)
- Test Summary TS-34080-002-001 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	34080
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Left Reel Payoff
Crimp Quality Equipment	Yes
Overview	MX150 Sealed and Unsealed Connector System
Product Name	MX150
UPC	884982337237

Physical

Gender	Male
Grip Code	22
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.365/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.70mm max.
Wire Size AWG	22
Wire Size mm²	0.50

Electrical

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	14V DC

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Application Specification	AS-34080-001-001
Packaging Specification	313025040-000
Product Specification	PS-34083-002-001
Sales Drawing	SD-34080-001-001
Test Summary	TS-34080-002-001

EU ELV

Compliant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

34080 Series

Use With

34675 MX150 2 Way Inline Male Assembly with TPA, 34091 MX150 1.50mm 3 Way Single Row Cable Seal

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
FA2 Mechanical Applicator for MX150 Terminals, 22 AWG, 0.35mm², 0.50mm² Wire	638083100
FA2 Pneumatic Feed Crimp Applicator for MX150 22 Grip Wire Seal Blade Terminals	638083110

This document was generated on 10/01/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[34080-1106](#)