

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0340813004

Status:

Active

Overview:

MX150 Sealed and Unsealed Connector System

Description:

MX150 Cable Seal Female Terminal, Gold Plating, 18 and 20 AWG, Left Reel Payoff

Documents:

Drawing (PDF)

Product Specification PS-34083-002-001 (PDF)

Application Specification AS-34083-002-001 (PDF)

Packaging Specification 313025040-000 (PDF)

Test Summary TS-34081-002-001 (PDF)

Datasheet (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Application

Comments

Crimp Quality Equipment

Overview

Product Name

UPC

Crimp Terminals

34081

Power, Wire-to-Board, Wire-to-Wire

Left Reel Payoff, Cable Seal

Yes

MX150 Sealed and Unsealed Connector System

MX150

822350084482

Physical

Gender

Grip Code

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Packaging Type

Plating min - Mating

Plating min - Termination

Termination Interface: Style

Wire Insulation Diameter

Wire Size AWG

Wire Size mm²

Female

18

High Performance Alloy (HPA)

Gold

Tin

0.367/g

Reel

0.762µm

2.540µm

Crimp or Compression

2.54mm max.

18, 20

0.75-1.00

Electrical

Current - Maximum per Contact

Voltage - Maximum

Contact Molex

14V DC

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Reference - Drawing Numbers

Application Specification

Packaging Specification

Product Specification

Sales Drawing

Test Summary

AS-34083-002-001

313025040-000

PS-34083-002-001

SD-34083-002-001

TS-34081-002-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2021)4569-DC (8 July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

34081 Series

Use With

33471 Single Row Sealed Connector, 33472 Dual Row Sealed Connector, 33476 Dual Row Hybrid Sealed Connector, 34062 Single Row 2-Way Cable Sealed Connector, 34250 Single Row 3-Way Cable Sealed Connector

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	Description	Product #
	Extraction Toolkit for MX150 Connectors	2002220700
	Extraction Tool for MX150L, MX150, PT Bulb Socket, iGrid, SPOX, and Wire-to-Motor Terminals	638131500

Hand Crimp Tool for [638199200](#)
Cable Seal Crimp
Terminals
FineAdjust Applicator[639018100](#)
for Cable Seal Crimp
Terminals

This document was generated on 09/13/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[34081-3004](#)