

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0348992080](#)
Status: **Active**
Overview: [MXP120 Sealed Connector System](#)
Description: MXP120 Sealed Male Blade Connector with 7.00mm Clip-Slot, 2 Circuit, Black Housing (T3-V2-S3), Backshell Interface Option 2, Key A

Documents:

Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-34900-0001-001 (PDF)	Product Literature (PDF)
Packaging Specification PK-31301-898-001 (PDF)	

Application tooling part link

Application Tooling Part Link	63824-6300
-------------------------------	------------

General

Product Family	Crimp Housings
Series	34899
Application	Automotive, Body Electronics, Sealed, Wire-to-Wire
Comments	See sales drawing for terminal information.
Overview	MXP120 Sealed Connector System
Polarization	A
Product Name	MXP120 Sealed
UPC	889056518741

Physical

Circuits (maximum)	2
Color - Resin	Black
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	3.500/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.00mm
Pitch - Termination Interface	4.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +125°C

Electrical

Current - Maximum per Contact	13.0A
-------------------------------	-------

Material Info

Reference - Drawing Numbers

Application Specification	AS-34900-0001-001
Packaging Specification	PK-31301-898-001
Sales Drawing	SD-34899-2001-001, SD-34899-6001-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[34899](#) Series

Mates With

MXP120 Female Receptacle [34900](#)

Use With

Tyco 1.2 MCON terminals
Or
Kostal
MLK 1.2 terminals

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Extraction Toolkit
for MXP120 Sealed
Connection System

[638246300](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[34899-2080](#)