

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0348993071](#)
Status: **Active**
Overview:
Description: MXP120 Sealed Male Blade Connector with 7.00mm Clip-Slot, 3 Circuit, Yellow SIR Housing (T3-V2-S2 - 125°C on-engine vibration), Wire Dress Cover Interface Option 2, Key B

Application tooling part link	
Application Tooling Part Link	63824-6300
General	
Product Family	Crimp Housings
Series	34899
Application	Automotive, Safety, Sealed, Wire-to-Wire
Comments	See sales drawing for terminal information.
Overview	120mm_sealed_connection_system_
Polarization	B
Product Name	MXP120 Sealed
UPC	889056518932
Physical	
Circuits (maximum)	3
Color - Resin	Yellow
Gender	Plug
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	4.512/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.00mm
Pitch - Termination Interface	4.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +125°C
Electrical	
Current - Maximum per Contact	13.0A
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-34900-0001-001
Packaging Specification	PK-31301-898-001
Sales Drawing	SD-34899-2001-001, SD-34899-6001-001

EU ELV Compliant	
EU RoHS Compliant REACH SVHC Not Contained Per - D(2021)4569-DC (8 July 2021) Halogen-Free Status Not Relevant For more information, please visit Contact US	China RoHS China ROHS ELV RoHS Phthalates
Not Relevant Compliant Not Contained	

Search Parts in this Series 34899 Series	
Mates With MXP120 Female Receptacle 34900	
Use With Tyco 1.2 MCON terminals Or Kostal MLK 1.2 terminals	
Application Tooling FAQ <i>Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.</i> Global	
Description	Product #
Extraction Toolkit for MXP120 Sealed Connection System	638246300

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[34899-3071](#)